





PART NAME	NEMA 4X PLASTIC BOX w/EXTERNAL MTG. BRKT.	PART No.	PN-1337-MB PN-1337-CMB PN-1337-DGMB	REVISION DATE	2-10-14
-----------	---	----------	-------------------------------------	---------------	---------



MATERIAL & FINISH:
 (-MB SUFFIX PART NO.) POLYCARBONATE UL94-HB, UV STABILIZED, SERVICE TEMPERATURE RANGE: -40°C TO $+120^\circ\text{C}$, LIGHT GRAY BODY & COVER.
 (-CMB SUFFIX PART NO.) SAME AS -MB EXCEPT CLEAR COVER.
 (-DGMB SUFFIX PART NO.) ABS UL94-HB, SERVICE TEMPERATURE RANGE: -40°C TO $+80^\circ\text{C}$, DARK GRAY BODY & COVER.

NOTES:
 1.) FOUR (4) M4 STAINLESS STEEL SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
 2.) BOXES DESIGNED TO MEET FOLLOWING STANDARDS:
 NEMA 1, 2, 4, 4X, 12, 13 AND IEC529-IP66 REQUIREMENTS.
 3.) ALL HOLE DIAMETERS HAVE $\pm .005$ [.12] TOLERANCE.
 ALL OTHER DIMENSIONS HAVE $\pm .015$ [.38] TOLERANCE.
 4.) ALL OUTSIDE DRAFT ANGLE: 1°
 ALL INSIDE DRAFT ANGLE: $1/2^\circ$
 5.) DIMENSIONS ARE INCH[MM]

BODY

COVER