



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .020$	W $\pm .010$	C $\pm .015$	M $\pm .020$	H $\pm .010$
P10-10FF	#10	.80 (20.32)	.38 (9.65)	.28 (7.11)	.55 (13.97)	.20 (5.08)

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. #12-10 AWG SOLID OR STRANDED COPPER WIRE
 - B. 347° F (175° C) MAX. TEMP. RATING
2. MATERIAL:
 - A. STAMPING - .04" (1.12) THK COPPER, TIN PLATED
3. PACKAGE QTY: STD. PKG. 50
 BULK PKG. 500
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS: CT-100, CT-160, CT-200



LISTED
587H
E52164



CERTIFIED
LR31212

A41238_04

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
04	2/01	KMD		DRAWING NUMBER WAS A41238A				#12-10 BARREL NON-INSULATED FLANGED FORK			
03	7-88	DW		REDRAWN WITH REVISIONS	07629						
REV	DATE	BY	CHK	DESCRIPTION	ECN	PM	APP	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								DAW		NONE	A41238

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[P10-10FF-L](#)