

**General ordering data**

Order No.	9019280000
Part designation	H25,0/30D 16 GE
Version	Wire-end ferrule, 25 mm ² , 16 mm, Colour code: DIN, yellow
EAN	4008190038380
Qty.	50 pc(s).

Technical data

Length	16 mm
Width	12 mm
Height	12 mm

Product data

Conductor rated cross-section	25 mm ²
AWG	3
Total length (L1)	30 mm
Contact surface length (L2)	16 mm
Contact surface diameter (D1)	7.3 mm
Collar diameter (D2)	11.2 mm
Metal sleeve thickness (S1)	0.2 mm
Plastic collar thickness (S2)	0.4 mm

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01

Classifications

eClass 5.1

27-40-02-01

Similar products

Order No.	Part designation	Version
0317000000	H25,0/30 BR	Wire-end ferrule, 25 mm², 16 mm, Colour code: Weidmüller, brown
9021190000	H25,0/30T SW	Wire-end ferrule, 25 mm², 16 mm, Colour code: Miscellaneous, black
0317100000	H25,0/36 BR	Wire-end ferrule, 25 mm², 22 mm, Colour code: Weidmüller, brown
9019300000	H25,0/36D GE	Wire-end ferrule, 25 mm², 22 mm, Colour code: DIN, yellow
9021200000	H25,0/36T SW	Wire-end ferrule, 25 mm², 22 mm, Colour code: Miscellaneous, black