



Ordering number **CA12333**
Description **1**

Family	Strada-T	FWHM	(simulated) Asym
Type	Assembly	Efficiency	(simulated) 89 %
LED	3J (GSPW16)	cd/lm	(simulated) 0.000
Color	Clear	Gerber File	Available
Diameter	19.6 x 15.5 mm		
Height	11.3 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	On production		


NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

D


C

B


A




Isometric view





20
fastening
Bottom view



Beam direction



10.9
With tape 11.3
Front view

Strada lens arrangement
recommendation

Top view

MATERIALS

Lens: PMMA

Tape(optional): PU Foam

Part no. with tape fastening: CA12333_Strada-T-DW

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



Ledil Oy
Tehdaskatu 13
FIN-24100 SALO
Finland

DRAWING TITLE

Datasheet STRADA-T-DW

DRAWN BY
ah

DATE
13.12.2011

SIZE
A4

DRAWING NUMBER

C12331

REV
1

CHECKED BY
vs

DATE
13.12.2011

DESIGNED BY
hh

DATE
17.05.2010

SCALE
2:1

WEIGHT(g)

SHEET
1/1

D

A