



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
▶ 2 mm system
▶ 2 mm safety system
▶ 4 mm system
▶ 4 mm sliding sleeve system
▶ 4 mm safety system
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ plugs ▶ plugs ▶ SLS 10 B

SLS 10 B

datasheet for SLS 10 B
article number: 931824101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 931 824-101
description:	Touch protected plug to assemble with solder connection for cables up to 2.5mm². Insulated by latching and sprung insulating sleeve, to be released by pressure on the lateral locking spring. plug with contact spring, 4mm diameter.
typ:	SLS 10 B rot/red
system:	4mm sliding sleeve system
order number:	931 824-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	30 A
Please consider derating curve!	
contact resistance:	5 mOhm
material	
contact material:	contact pin: brass contact spring: copper - beryllium
contact surface material:	nickel
housing material:	POM
environmental conditions:	
temperature range:	-25 °C to +80 °C
drawing	
	