

# Double Row Terminal Blocks

## Kulka® 601/801 GP Series

### 300 Volts AC/DC (Classes B/C)

601 Series only

### 150 Volts AC/DC (Class C)

801 Series only



601 GP 06

#### Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #6-32 Binder Head, Phil-Slot, Steel
- Terminals, Plated Brass
- 1-23 Poles
- 7/16" Centers
- Wire Range With Wire Binding Screw #12 - #22 AWG – 20 Amps
- 801 Series (Riveted KT's) - see page 105
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- 
- RoHS Compliant

| Kulka®<br>Catalog # | # of poles | Dimensions |       |
|---------------------|------------|------------|-------|
|                     |            | A          | B     |
| 601 GP 01           | 1          | 1.19       | 0.88  |
| 601 GP 02           | 2          | 1.62       | 1.31  |
| 601 GP 03           | 3          | 2.06       | 1.75  |
| 601 GP 04           | 4          | 2.50       | 2.19  |
| 601 GP 05           | 5          | 2.94       | 2.63  |
| 601 GP 06           | 6          | 3.37       | 3.06  |
| 601 GP 07           | 7          | 3.81       | 3.50  |
| 601 GP 08           | 8          | 4.25       | 3.94  |
| 601 GP 09           | 9          | 4.69       | 4.38  |
| 601 GP 10           | 10         | 5.12       | 4.81  |
| 601 GP 11           | 11         | 5.56       | 5.25  |
| 601 GP 12           | 12         | 6.00       | 5.69  |
| 601 GP 13           | 13         | 6.44       | 6.13  |
| 601 GP 14           | 14         | 6.87       | 6.56  |
| 601 GP 15           | 15         | 7.31       | 7.00  |
| 601 GP 16           | 16         | 7.75       | 7.44  |
| 601 GP 17           | 17         | 8.19       | 7.88  |
| 601 GP 18           | 18         | 8.62       | 8.31  |
| 601 GP 19           | 19         | 9.06       | 8.75  |
| 601 GP 20           | 20         | 9.50       | 9.19  |
| 601 GP 21           | 21         | 9.94       | 9.63  |
| 601 GP 22           | 22         | 10.37      | 10.06 |
| 601 GP 23           | 23         | 10.81      | 10.50 |

mm=dim X 25.4

For electronic drawings or 2D/3D CAD data, submit request at [www.marathonsp.com/drawings.html](http://www.marathonsp.com/drawings.html)

#### Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

| CATALOG #<br>MSP KULKA | PRODUCT<br>DESCRIPTION        | PAGE<br>REFERENCE |
|------------------------|-------------------------------|-------------------|
| KT37                   | Full Quick Connect (0° Flat)  | See Page 105      |
| KT38                   | Full Quick Connect (45° Bend) | See Page 105      |
| KT39                   | Full Quick Connect (90° Bend) | See Page 105      |
| KT43                   | Half Quick Connect (0° Flat)  | See Page 105      |
| KT44                   | Half Quick Connect (45° Bend) | See Page 105      |
| KT45                   | Half Quick Connect (90° Bend) | See Page 105      |
| ST                     | Full Solder                   | See Page 106      |
| 3/4 ST                 | Half Solder                   | See Page 106      |
| Y                      | Feed Thru Solder (.422)       | See Page 106      |
| YSY                    | Feed Thru Solder (.687)       | See Page 106      |
| J 601                  | Line to Line Jumper           | See Page 107      |
| 601 RJ(S)              | Multiple Position Jumper      | See Page 107      |
| 3765                   | Wire Clamp Screw              | See Page 107      |
| 3760                   | Wire Clamp Screw              | See Page 107      |
| 2102                   | Stud                          | See Page 109      |
| 2104                   | Feed Thru Solder              | See Page 109      |
| 2108                   | Individual Screw Terminals    | See Page 109      |
| PSB                    | Phil-Slot Brass Screw         | Consult C/S       |

Quick Connects: .032" x .250"

See pages 104-115 for terminal block accessories

