

MATERIALS AND FINISHES

PART NO. 73415-4760/73415-4761
73415-4762/73415-4763
73415-4765

BODY
BRASS
PLATED:50u" MIN COPPER UNDERCOAT.
100~200u" NICKEL UNDERCOAT.
2u" MIN GOLD PLATING.


CENTER CONTACT
BERYLLIUM COPPER
PLATED:10u" MIN GOLD PLATING

INSULATOR
TEFLON

WITHSTAND 48HRS SALT SPRAY TEST

Note:

1. Part No.73415-4761 WITHOUT CONTACT PART
2. 73415-4762 WITH CUSTOMER REQUEST PACKAGE
3. Part No.73415-4763 USE PART NO.73415-4760 WITH 500PCS BY BAG






PART NO. 73415-4764

BODY
BERYLLIUM COPPER
PLATED TRI-METAL

CENTER CONTACT
BERYLLIUM COPPER
PLATED GOLD

INSULATOR
TEFLON



73415-4767	NON-MAGNETIC	1 PIECE 73415-4764 PER BAG
73415-4766	GENERAL TYPE	1 PIECE 73415-4760 PER BAG
73415-4765	GENERAL TYPE	SPECIFIC LABEL ON OUTER BOX
73415-4764	NON-MAGNETIC	500pcs BY ONE BAG
73415-4763	GENERAL TYPE	500pcs BY ONE BAG
73415-4762	GENERAL TYPE	SEE NOTE 2
73415-4761	GENERAL TYPE	SEE NOTE 1
73415-4760	GENERAL TYPE	1000pcs BY ONE BAG
PART NO.	DESCRIPTION	PACKAGING

PS-89675-0320

PRODUCT SPECIFICATION

SPECIFICATION

DESCRIPTION

CHG: PS WAS
PS-73599-0220,
DELETED AS.

EC NO: URF2011-0430 2011/01/17
DRWN: JLEE02 2011/01/17
CHKD: SSS 2011/01/17
APPR: JWIENER 2011/01/17

REV DESCRIPTION
C6

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± --- ± ---
1 PLACE ± --- ± ---
ANGULAR ± 2 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN
DRAWN BY DATE
JLEE 2007/07/23
CHECKED BY DATE
TFLAHERTY 2007/07/23
APPROVED BY DATE
JWIENER 2007/07/23
MATERIAL NO.
SEE TABLE
SIZE
C

SCALE DESIGN UNITS
METRIC
THIRD ANGLE PROJECTION
TITLE
SSMCX JACK, 50 OHM
CABLE TYPE (.047, 1.3MM)
SSMCX-JC
molex MOLEX INCORPORATED
DOCUMENT NO.
SD-73415-476
SHEET NO.
1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION