


Specifications:

Resonant Frequency (Hz)	400 ± 100
Operating Voltage (Vdc)	4.0 ~ 8.0
Rated Voltage (Vdc)	6.0
Current Consumption Max. (mA)	40 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-30 ~ +80
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Wire	26 AWG
Weight (Grams)	7.8
Options	or other options contact factory

Dimensions: (units: mm)

PK-16N04WA-06



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PK-16N04W-06](#)