


Item no.:	745-352
Product description:	PCB TERMINAL STRIP 2 SOLDER PINS / POLE 2 POLE PIN SPACING 10 MM / 0.394 IN WITHOUT FIXING FLANGE



Produkt kann von Bild abweichen / product may differ

Packing unit 96 pieces

Product group	4 (Printed Circuit)
Weight	11.005 g
Color	gray
No. of connection Points	2
No. of potentials	2
pole count	2
Height	23 mm
Height	0.906 in
Width	19.1 mm
Width	0.752 in
Depth	29.1 mm
Depth	1.15 in
Pin spacing from	10 mm
Pin spacing from	0.394 in
Pollution degree	2
Measured voltage EN	1000 V
Measured shock voltage	8 kV
Current intensity EN	41 A
Pollution degree	2
Measured voltage EN	1000 V

Measured shock voltage
Current intensity EN

8 kV
41 A



Connection method	CAGE CLAMP® CONNECTION
Cross section [mm²]	0.2 - 6 mm²
Wiring method	solid
Cross section [mm²]	0.2 - 6 mm²
Cross section [mm²]	0.25 - 4 mm²
Cross section [mm²]	0.25 - 4 mm²
Cross section [AWG]	24 - 10 AWG
Strip length from	11 mm
Strip length to	12 mm
Material group	I
xxx-xxx/000-006	blue
xxx-xxx/000-009	light gray
xxx-xxx/000-016	green-yellow
xxx-xxx/000-017	light green
xxx-xxx/005-000	with fixing flange
xxx-xxx/005-xxx	with fixing flange



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
745-352	CCA	NL6296	630	41	0,02-6
745-352	cURus	E45172	300/150/300	30/30/10	24-10
745-352	KEMA	2076500.02	630	41	0,02-6
745-352	KEMA	2097989.01	630	41	0,02-6

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected