


# ED115/XDS



**2-12 poles, Spacing 7.5 mm**

insert required no. of poles **x**

How to order see page 5



## Ratings:

|                        |                  |                           |
|------------------------|------------------|---------------------------|
| Rated Voltage          | <b>300V</b>      | <b>500 V</b>              |
| Rated Current          | <b>20 A</b>      | <b>24 A (T60)</b>         |
| Wire Size              | <b>AWG 22-14</b> | <b>2.5 mm<sup>2</sup></b> |
| Test Voltage           |                  | <b>3.0 kV</b>             |
| Rated Torque/ScrewSize |                  | <b>0.5 Nm/M3</b>          |

## Max. Rated Cross Section

|                             |                           |
|-----------------------------|---------------------------|
| Single Wire (solid)         | <b>2.5 mm<sup>2</sup></b> |
| Stranded Wire (flexible)    | <b>1.5 mm<sup>2</sup></b> |
| Stranded wire with Ferrules | <b>1.5 mm<sup>2</sup></b> |

## Dimensions

|                   |               |
|-------------------|---------------|
| Spacing           | <b>7.5 mm</b> |
| PCB Hole Diameter | <b>1.3 mm</b> |
| Stripped Length   | <b>6.0 mm</b> |

## Materials

|                     |                        |
|---------------------|------------------------|
| Insulating Material | <b>PA</b>              |
| Flammability Class  | <b>UL94 V-0</b>        |
| Temperature Range   | <b>-30°C/+105°C</b>    |
| Terminal Block      | <b>CuZn</b>            |
| Wire Guard          | <b>Stainless Steel</b> |

## Color

Grey

