




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	PRINT-ON HEIGHT "A" inches [mm] +/- .031	WIDTH "B" inches [mm] +/- .031	"C" LENGTH	MARKERS PER CARDS	STD. PKG. CARDS	STD. CTN. CARDS
PSWMH-375Y	.375 [9.5]	.375 [9.5]	.75 [19.1]	50	25	100
PSWMH-750Y	.375 [9.5]	.75 [19.1]	.75 [19.1]	24	25	100

NOTES:
1. MILLIMETER ARE IN [].
2. 25 CARDS PER BOX.



										CAD FILENAME/LAYERS		100295FE-DC-C10633/01B			
										PANDUIT CORP. TINLEY PARK, ILLINOIS					
										CUSTOMER DRAWING SELF-LAM. WIRE MARKER CARDS PSWMH-***Y					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
															
1	3/29/11	RVU		UPDATE ON TABLE, CHG. FROM B SIZE TO A SIZE. UPDATE TOL. AND MATERIAL.		6337	R			DRAWN BY RVU		MAT'L: GMV3 SELF-LAM. VINYL		SCALE NTS	
0	1/9/08	RVU		DRAWING RELEASE		5261	R			DATE 1/9/08		DRAWING NO. C10633		DWG A SIZE	
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	CHK'D				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCMH-23](#) [PCMH-1](#) [PCMH-5](#) [PCMH-9](#) [PCMH-12](#) [PCMH-2](#) [PCMH-20](#) [PCMH-15](#) [PCMH-3](#) [PCMH-21](#) [PCMH-18](#)
[PCMH-19](#) [PCMH-17](#) [PCMH-0](#) [PCMH-8](#) [PCMH-7](#) [PCMH-25](#) [PCMH-22](#) [PCMH-11](#) [PCMH-4](#) [PCMH-16](#) [PCMH-6](#)
[PCMH-13](#) [PCMH-10](#) [PSWMH-750Y](#) [PCMH-14](#) [PCMH-24](#)