


CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



NOTE:
1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

3. TERM. NOS. FOR REFERENCE ONLY.

▲ 4. CONTACT MATERIAL: GOLD
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC
350MILLIAMP, 110VAC/DC

6. CONTACT RATING: (NON-SWITCHING) 5A

7. OPERATING FORCE: 425±100CM/STANDARD

8. OPERATING TEMP: -30°C TO 85°C

▲ 9. CIRCUIT SP: 3 POSITION 30° INDEX.



10. DIELECTRIC STRENGTH: 1000V RMS MIN. @ SEA LEVEL.

▲ 11. HARDWARE SUPPLIED ON SWITCH:


LOCKWASHER, HEXNUT, STOP RING

12. ▲DENOTES CRITICAL PARAMETER.

13. 2002/95/EC (ROHS) COMPLIANT



ISOMETERIC



E-SWITCH®

TITLE KC13A13.001NPF

SCALE 1.5:1

DATE 5/30/2006

DR CT

DWG G510579

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

| | | | | |
|-----|--------|-------------------------|---------|----|
| A | 16057 | RELEASED FOR PRODUCTION | 5/30/06 | CT |
| REV | PCR NO | DESCRIPTION | DATE | BY |