

FUSE STRIPS FOR DIESEL RATED 36V


RoHS


Description

Non-housed fuse strips for Diesel vehicles.
 Current rating 25A - 150A, 36 VDC. 90° fork type lugs.

Dimensions

Dimensions in mm



Ratings

Part Number	Current Rating	Typ. Voltage Drop
156.5610.525_	25 A*	70 mV
156.5610.530_	30 A	70 mV
156.5610.540_	40 A*	70 mV
156.5610.550_	50 A	70 mV
156.5610.560_	60 A*	70 mV
156.5610.570_	70 A*	70 mV
156.5610.580_	80 A	70 mV
156.5610.610_	100 A	70 mV
156.5610.611_	120 A*	70 mV
156.5610.612_	125 A*	70 mV
156.5610.615_	150 A*	70 mV
156.5610.625_	250A*	70 mV


Specifications

Metal Parts: Zinc-alloy
 Complies with: DIN 72581/2

Ordering Information

Part Number	Package Size
156.5610.xxx1	100
156.5610.xxx2	2000

Pre-arcing Time-limits



FI = 1.00 (max. operating current: $1.0 \times I_{rat}$ at 23°C)

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)
130	3,600 s / –
250	– / 60 s

*Not mentioned in the standards
 Corresponding holder see Section "Fuse Holders."

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[156.5610.6251](#) [156.5610.6252](#)