

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

DWN

APVD

AJ

16

S

REVISED PER ECO-12-008922

06SEP12

MGM

WM

1


2

3

4

11.07 MAX
[.436]

30.48 MAX
[1.200]




15.90 REF
[.626]

4.78
[.188]

11.13
[.438]

5.56
[.219]



RECOMMENDED STRIP LENGTH

SCALE 2:1

	OBSOLETE	AMP & 3-331351-4	ITT-3474	220029-1	-	50428-1	225136-3	331355	3-331351-4
SUPERSEDED BY	2-329452-2	00779-M39012/17B0007 YY WW	RG-142/U,142A/U & 142B/U	69478-1	-	329099	2-331369-4	2-331355-1	2-331351-9
SUPERSEDED BY	2-225396-1	00779-M39012/17B0006 YY WW	RG-141/U &141A/U	69478-1	-	50427-1	2-331369-4	2-331355-1	2-331351-8
	OBSOLETE	00779-M39012/17B0005 YY WW	RG-55/U,55A/U,55B/U & 223/U	69478-1	-	329099	2-331369-3	2-331355-1	2-331351-7
SUPERSEDED BY	225396-9	AMP & 2-331351-6	RG-180/U,180A/U &195/U	69477-2	-	329461	1-331368-4	2-331355-2	2-331351-6
SUPERSEDED BY	225396-8	AMP & 2-331351-5	RG-179/U & 187/U	220009-1	21427-2	2-328666-3	1-331368-4	2-331355-2	2-331351-5
		AMP & 2-331351-4	RG-174/U & 188/U	220009-1	21427-2	2-328666-3	1-331368-2	2-331355-2	2-331351-4
	OBSOLETE	AMP & 2-331351-2	AMPHENOL 21-597	69477-2	-	329461	1-331368-2	2-331355-2	2-332351-2
		00779-M39012/17B0004 YY WW	RG-58/U,58A/U,58B/U & 58C/U	69478-1	-	9-50427-3	2-331369-3	2-331355-1	2-331351-1
		00779-M39012/17B0008 YY WW	RG-59/U,59A/U,59B/U,62/U,62A/U & 62B/U	69477-1	-	9-50428-4	3-331368-9	331355	331351
		STAMPING	CABLE SIZE	CRIMP TOOL	④ BUSHING QTY=1	③ FERRULE QTY=1	② CONTACT QTY=1	① JACK ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
B. SCOTT
CHK
J. LIPPERT
APVD

DIMENSIONS:
INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.41 [016]
3 PLC ± -
4 PLC ± -
ANGLES
FINISH

0
1
2
3
4

MATERIAL
-

FINISH
-

PRODUCT SPEC
108-12020

APPLICATION SPEC
-

SIZE
A1

CAGE CODE
00779

DRAWING NO
331351

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 1

REV S

TE Connectivity

JACK,DUAL CRIMP,
SERIES BNC

4805 (3/11)