

QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
-12.00	0.200	120	DC	Power Sources (Desk-Top)		STAR-9005	15	C
-12.00	0.200	120	DC	Power Sources (Desk-Top)		STAR-9006	15	C
-12.00	0.300	120	DC	Power Sources (Desk-Top)		STAR-9007	15	C
1.25	5.000	117	AC	Power Transformers		P-6133	47	A
1.25	10.000	117/107	AC	Power Transformers		P-6454	47	A
2.50	0.500	120	DC	Power Sources (Wall Plug-In)		STA-4125T	13	A
2.50	1.000	117	AC	Power Transformers		P-8629	47	A
2.50	1.500	117	AC	Power Transformers		P-4026	47	A
2.50	3.000	117	AC	Power Transformers		P-6467	47	B
2.50	5.000	117	AC	Power Transformers	*	P-6133	47	A
2.50	10.000	117	AC	Power Transformers		P-6135	47	B
2.50	10.000	117/107	AC	Power Transformers	*	P-6454	47	A
2.90	0.320	230/50HZ	AC	Power Sources (Wall Plug-In)		STAF-1433F	17	A
3.00	0.120	230/50HZ	AC	Power Sources (Wall Plug-In)		STAF-2099F	17	A
3.00	0.350	120	DC	Power Sources (Wall Plug-In)		STA-4130	13	A
3.00	0.400	120	DC	Power Sources (Wall Plug-In)		STA-3530A	13	A
3.00	0.500	120	DC	Power Sources (Wall Plug-In)		STA-3530	13	A
3.15	0.300	117	AC	Power Transformers		P-8385	47	B
3.15	0.600	117	AC	Power Transformers		P-6465	47	B
3.15	0.600	230	AC	Power Transformers		P-8705	47	C
3.15	1.200	117	AC	Power Transformers		P-6134	47	C
3.15	3.000	117	AC	Power Transformers		P-6466	47	D
3.15	4.000	117	AC	Power Transformers		P-8648	47	D
3.15	5.000	117	AC	Power Transformers		P-8649	47	D
3.15	6.000	117	AC	Power Transformers		P-3064	47	D
3.15	6.000	117/107	AC	Power Transformers		P-6456	47	E
3.15	8.000	117	AC	Power Transformers		P-8651	47	E
3.15	10.000	117	AC	Power Transformers		P-6464	47	E
3.15	10.000	117/107	AC	Power Transformers		P-6308	47	E
3.15	20.000	117/107	AC	Power Transformers		P-6309	47	F
3.75	4.000	117	AC	Power Transformers		P-5015	47	F
3.75	8.000	117	AC	Power Transformers		P-6138	47	F
4.00	0.188	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-1	33	A
4.00	0.376	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-1	33	A
4.00	0.562	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-11	33	B
4.00	1.130	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-11	33	B
4.40	0.400	120	DC	Power Sources (Wall Plug-In)		STA-3540	13	B
4.50	0.120	230/50HZ	AC	Power Sources (Wall Plug-In)		STAF-0418F	17	A
4.50	0.300	120	AC	Power Sources (Wall Plug-In)		STA-3545B	13	B
4.50	0.350	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-3924F	17	A
4.80	0.500	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-1847F	17	A
5.00	0.110	115	AC	Printed Circuit Transformers		SW-210	29	A
5.00	0.110	115/230	AC	Printed Circuit Transformers		DSW-210	29	A
5.00	0.120	115/230	AC	Printed Circuit Transformers		LB-610	27	B
5.00	0.200	115/230	AC	Printed Circuit Transformers		LB-210	27	A
5.00	0.220	115	AC	Printed Circuit Transformers		SW-210	29	A
5.00	0.220	115/230	AC	Printed Circuit Transformers		DSW-210	29	A
5.00	0.250	115	AC	Printed Circuit Transformers		SW-310	29	A
5.00	0.250	115/230	AC	Printed Circuit Transformers		DSW-310	29	A



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
5.00	0.300	115/230	AC	Printed Circuit Transformers		LB-310	27	A
5.00	0.400	115/230	AC	Printed Circuit Transformers		LB-210	27	A
5.00	0.400	115/230	AC	Printed Circuit Transformers		LB-410	27	A
5.00	0.500	115	AC	Printed Circuit Transformers		SW-310	29	A
5.00	0.500	115/230	AC	Printed Circuit Transformers		LB-510	27	A
5.00	0.500	115/230	AC	Printed Circuit Transformers		DSW-310	29	A
5.00	0.500	115/230	AC	TransGlobal International (PC Mount)		TG2H-10	23	A
5.00	0.600	115	AC	Printed Circuit Transformers		SW-410	29	A
5.00	0.600	115/230	AC	Printed Circuit Transformers		LB-310	27	A
5.00	0.600	115/230	AC	Printed Circuit Transformers		LB-610	27	B
5.00	0.600	115/230	AC	Printed Circuit Transformers		DSW-410	29	A
5.00	0.600	120	DC	Power Sources (Wall Plug-In)		STA-4850	13	B
5.00	0.800	115/230	AC	Printed Circuit Transformers		LB-410	27	A
5.00	0.800	120	DC	Power Sources (Desk-Top)		STAR-9005	15	C
5.00	1.000	115/230	AC	Printed Circuit Transformers		LB-510	27	A
5.00	1.000	115/230	AC	TransGlobal International (PC Mount)		TG05-10	23	A
5.00	1.000	117	AC	Power Transformers		P-8652	47	F
5.00	1.000	120	DC	Power Sources (Desk-Top)		STAR-9001	15	C
5.00	1.000	120	DC	Power Sources (Desk-Top)		STAR-9006	15	C
5.00	1.000	120	DC	Power Sources (Desk-Top)		STAR-9007	15	C
5.00	1.200	115	AC	Printed Circuit Transformers		SW-410	29	A
5.00	1.200	115	AC	Printed Circuit Transformers		SW-510	29	A
5.00	1.200	115/230	AC	Printed Circuit Transformers		LB-1210	27	B
5.00	1.200	115/230	AC	Printed Circuit Transformers		DSW-410	29	A
5.00	1.200	115/230	AC	Printed Circuit Transformers		DSW-510	29	A
5.00	1.500	120	DC	Power Sources (Desk-Top)		STAR-9002	15	C
5.00	2.000	115	AC	Printed Circuit Transformers		SW-610	29	A
5.00	2.000	115/230	AC	Printed Circuit Transformers		DSW-610	29	A
5.00	2.000	115/230	AC	TransGlobal International (PC Mount)		TG10-10	23	A
5.00	2.000	117	AC	Power Transformers		P-8653	47	G
5.00	2.400	115	AC	Printed Circuit Transformers		SW-510	29	A
5.00	2.400	115/230	AC	Printed Circuit Transformers		LB-1210	27	B
5.00	2.400	115/230	AC	Printed Circuit Transformers		DSW-510	29	A
5.00	3.000	117	AC	Power Transformers	*	P-6467	47	B
5.00	3.000	117	AC	Power Transformers		P-8380	47	G
5.00	4.000	115	AC	Printed Circuit Transformers		SW-610	29	A
5.00	4.000	115/230	AC	Printed Circuit Transformers		DSW-610	29	A
5.00	4.000	115/230	AC	TransGlobal International (PC Mount)		TG20-10	23	A
5.00	4.000	117	AC	Power Transformers		P-5016	47	G
5.00	4.000	117	AC	Power Transformers		P-8654	47	G
5.00	5.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-10	21	A
5.00	5.000	117/107	AC	Power Transformers		P-6458	47	G
5.00	6.000	115/230	AC	TransGlobal International (PC Mount)		TG30-10	23	A
5.00	6.000	117	AC	Power Transformers		P-8655	48	A
5.00	8.000	117	AC	Power Transformers		P-8656	48	A
5.00	8.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-10	21	A
5.00	10.000	117	AC	Power Transformers	*	P-6135	47	B
5.00	10.000	117	AC	Power Transformers		P-6461	48	A
5.00	11.200	115/230	AC	TransGlobal International (PC Mount)		TG56-10	23	A



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
5.00	16.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-10	21	A
5.00	26.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-10	21	A
5.00	35.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-10	21	A
5.20	1.000	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-1848F	17	B
6.00	0.100	120	DC	Power Sources (Wall Plug-In)		STA-3560B	13	B
6.00	0.200	120	DC	Power Sources (Wall Plug-In)		STA-3560	13	C
6.00	0.300	120	DC	Power Sources (Wall Plug-In)		STA-3560A	13	C
6.00	0.330	115/230	AC	Printed Circuit Transformers		LB-412	27	B
6.00	0.417	115/230	AC	Printed Circuit Transformers		LB-512	27	B
6.00	0.500	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-0381F	17	B
6.00	0.600	120	DC	Power Sources (Wall Plug-In)		STA-4160	13	C
6.00	0.667	115/230	AC	Printed Circuit Transformers		LB-412	27	B
6.00	0.800	120	DC	Power Sources (Wall Plug-In)		STA-4160A	13	C
6.00	0.833	115/230	AC	Printed Circuit Transformers		LB-512	27	B
6.00	1.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6375	52	C
6.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4860	13	D
6.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4860-4	13	D
6.00	1.000	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-0797F	17	B
6.00	1.200	120	DC	Power Sources (Wall Plug-In)		STA-4860A	13	D
6.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6375	52	C
6.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6376	52	C
6.00	2.000	120	DC	Power Sources (Wall Plug-In)		STA-5760	13	D
6.00	3.300	120	AC	Power Sources (Desk-Top)		STA-5760A	13	E
6.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6376	52	C
6.20	0.300	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-2100F	17	B
6.20	0.350	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-0834F	17	B
6.30	0.090	115	AC	Printed Circuit Transformers		SW-212	29	B
6.30	0.090	115/230	AC	Printed Circuit Transformers		DSW-212	29	B
6.30	0.180	115	AC	Printed Circuit Transformers		SW-212	29	B
6.30	0.180	115/230	AC	Printed Circuit Transformers		DSW-212	29	B
6.30	0.200	115	AC	Printed Circuit Transformers		SW-312	29	B
6.30	0.200	115/230	AC	Printed Circuit Transformers		DSW-312	29	B
6.30	0.300	117	AC	Power Transformers	*	P-8385	47	B
6.30	0.350	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-18	33	C
6.30	0.400	115	AC	Printed Circuit Transformers		SW-312	29	B
6.30	0.400	115/230	AC	Printed Circuit Transformers		DSW-312	29	B
6.30	0.400	115/230	AC	TransGlobal International (PC Mount)		TG2H-12	23	B
6.30	0.450	115/230	AC	Printed Circuit Transformers		LB-612	27	C
6.30	0.500	115	AC	Printed Circuit Transformers		SW-412	29	B
6.30	0.500	115/230	AC	Printed Circuit Transformers		DSW-412	29	B
6.30	0.600	117	AC	Power Transformers	*	P-6465	47	B
6.30	0.600	230	AC	Power Transformers	*	P-8705	47	C
6.30	0.700	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-18	33	C
6.30	0.800	115/230	AC	TransGlobal International (PC Mount)		TG05-12	23	B
6.30	0.900	115/230	AC	Printed Circuit Transformers		LB-1212	27	C
6.30	0.900	115/230	AC	Printed Circuit Transformers		LB-612	27	C
6.30	1.000	115	AC	Printed Circuit Transformers		SW-412	29	B
6.30	1.000	115	AC	Printed Circuit Transformers		SW-512	29	B
6.30	1.000	115/230	AC	Printed Circuit Transformers		DSW-412	29	B



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
6.30	1.000	115/230	AC	Printed Circuit Transformers		DSW-512	29	B
6.30	1.000	117	AC	Power Transformers		P-8389	47	C
6.30	1.000	117	AC	Power Transformers		P-8384	48	C
6.30	1.200	117	AC	Power Transformers	*	P-6134	47	C
6.30	1.200	117	AC	Power Transformers		P-8190	47	C
6.30	1.500	117	AC	Power Transformers		P-8550	48	D
6.30	1.600	115	AC	Printed Circuit Transformers		SW-612	29	B
6.30	1.600	115/230	AC	Printed Circuit Transformers		DSW-612	29	B
6.30	1.600	115/230	AC	TransGlobal International (PC Mount)		TG10-12	23	B
6.30	1.800	115/230	AC	Printed Circuit Transformers		LB-1212	27	C
6.30	2.000	115	AC	Printed Circuit Transformers		SW-512	29	B
6.30	2.000	115/230	AC	Printed Circuit Transformers		DSW-512	29	B
6.30	2.000	117	AC	Power Transformers		P-8130	48	D
6.30	2.000	230	AC	Power Transformers		P-8715	48	D
6.30	3.000	117	AC	Power Transformers	*	P-6466	47	D
6.30	3.000	117	AC	Power Transformers		P-8358	48	D
6.30	3.200	115	AC	Printed Circuit Transformers		SW-612	29	B
6.30	3.200	115/230	AC	Printed Circuit Transformers		DSW-612	29	B
6.30	3.200	115/230	AC	TransGlobal International (PC Mount)		TG20-12	23	B
6.30	3.500	117	AC	Power Transformers (Multiple Secondary)	*	P-6429	52	A
6.30	4.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-12	21	B
6.30	4.000	117	AC	Power Transformers	*	P-8648	47	D
6.30	4.000	117	AC	Power Transformers		P-8641	48	E
6.30	4.000	230	AC	Power Transformers		P-8716	48	E
6.30	4.800	115/230	AC	TransGlobal International (PC Mount)		TG30-12	23	B
6.30	5.000	117	AC	Power Transformers	*	P-8649	47	D
6.30	6.000	117	AC	Power Transformers	*	P-3064	47	D
6.30	6.000	117	AC	Power Transformers		P-8642	48	E
6.30	6.000	117/107	AC	Power Transformers	*	P-6456	47	E
6.30	6.800	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-12	21	B
6.30	8.000	117	AC	Power Transformers	*	P-8651	47	E
6.30	8.800	115/230	AC	TransGlobal International (PC Mount)		TG56-12	23	B
6.30	10.000	117	AC	Power Transformers	*	P-6464	47	E
6.30	10.000	117	AC	Power Transformers		P-8644	48	E
6.30	10.000	117/107	AC	Power Transformers	*	P-6308	47	E
6.30	12.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-12	21	B
6.30	20.000	117/107	AC	Power Transformers	*	P-6309	47	F
6.30	20.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-12	21	B
6.30	28.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-12	21	B
7.00	0.250	115	AC	Power Transformers		P-8553	48	F
7.00	0.250	115/230	AC	Power Transformers		P-8577	48	F
7.00	1.000	115	AC	Power Transformers		P-8555	48	F
7.00	2.000	115	AC	Power Transformers		P-8556	48	F
7.00	4.000	115	AC	Power Transformers		P-8557	48	G
7.00	6.000	115	AC	Power Transformers		P-8558	48	G
7.50	0.100	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-2	33	A
7.50	0.100	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-46	33	A
7.50	0.100	120	DC	Power Sources (Wall Plug-In)		STA-3575	13	E
7.50	0.150	115/230	AC	Printed Circuit Transformers		LB-215	27	C



White-Rodgers • Emerson Electric Co.
9797 Reavis Road • St. Louis, MO 63123
(314) 865-8799 • Fax (314) 638-2400



STANCOR 109

QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
7.50	0.200	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-2	33	A
7.50	0.200	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-46	33	A
7.50	0.225	115/230	AC	Printed Circuit Transformers		LB-315	27	C
7.50	0.300	115/230	AC	Printed Circuit Transformers		LB-215	27	C
7.50	0.300	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-12	33	C
7.50	0.300	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-47	33	C
7.50	0.300	120	DC	Power Sources (Wall Plug-In)		STA-3575A	13	E
7.50	0.300	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-2243F	17	C
7.50	0.450	115/230	AC	Printed Circuit Transformers		LB-315	27	C
7.50	0.500	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-22	33	E
7.50	0.500	120	DC	Power Sources (Wall Plug-In)		STA-4175A	13	F
7.50	0.600	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-12	33	C
7.50	0.600	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-47	33	C
7.50	1.000	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-22	33	E
7.50	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4875	13	E
7.50	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4875-4	13	F
7.50	1.500	120	DC	Power Sources (Wall Plug-In)		STA-5775	13	F
7.50	4.000	117	AC	Power Transformers	*	P-5015	47	F
7.50	8.000	117	AC	Power Transformers	*	P-6138	47	F
8.00	0.070	115	AC	Printed Circuit Transformers		SW-216	29	C
8.00	0.070	115/230	AC	Printed Circuit Transformers		DSW-216	29	C
8.00	0.140	115	AC	Printed Circuit Transformers		SW-216	29	C
8.00	0.140	115/230	AC	Printed Circuit Transformers		DSW-216	29	C
8.00	0.150	115	AC	Printed Circuit Transformers		SW-316	29	C
8.00	0.150	115/230	AC	Printed Circuit Transformers		DSW-316	29	C
8.00	0.188	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-1	33	A
8.00	0.280	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-19	33	C
8.00	0.300	115	AC	Printed Circuit Transformers		SW-316	29	C
8.00	0.300	115/230	AC	Printed Circuit Transformers		DSW-316	29	C
8.00	0.300	115/230	AC	TransGlobal International (PC Mount)		TG2H-16	23	C
8.00	0.350	115/230	AC	Printed Circuit Transformers		LB-616	27	D
8.00	0.400	115	AC	Printed Circuit Transformers		SW-416	29	C
8.00	0.400	115/230	AC	Printed Circuit Transformers		DSW-416	29	C
8.00	0.560	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-19	33	C
8.00	0.562	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-11	33	B
8.00	0.620	115/230	AC	TransGlobal International (PC Mount)		TG05-16	23	C
8.00	0.700	115/230	AC	Printed Circuit Transformers		LB-1216	27	D
8.00	0.700	115/230	AC	Printed Circuit Transformers		LB-616	27	D
8.00	0.800	115	AC	Printed Circuit Transformers		SW-416	29	C
8.00	0.800	115	AC	Printed Circuit Transformers		SW-516	29	C
8.00	0.800	115/230	AC	Printed Circuit Transformers		DSW-416	29	C
8.00	0.800	115/230	AC	Printed Circuit Transformers		DSW-516	29	C
8.00	1.250	115	AC	Printed Circuit Transformers		SW-616	29	C
8.00	1.250	115/230	AC	Printed Circuit Transformers		DSW-616	29	C
8.00	1.250	115/230	AC	TransGlobal International (PC Mount)		TG10-16	23	C
8.00	1.400	115/230	AC	Printed Circuit Transformers		LB-1216	27	D
8.00	1.500	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-56	33	E
8.00	1.600	115	AC	Printed Circuit Transformers		SW-516	29	C
8.00	1.600	115/230	AC	Printed Circuit Transformers		DSW-516	29	C



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
8.00	2.500	115	AC	Printed Circuit Transformers		SW-616	29	C
8.00	2.500	115/230	AC	Printed Circuit Transformers		DSW-616	29	C
8.00	2.500	115/230	AC	TransGlobal International (PC Mount)		TG20-16	23	C
8.00	3.000	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-56	33	E
8.00	3.200	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-16	21	C
8.00	3.800	115/230	AC	TransGlobal International (PC Mount)		TG30-16	23	C
8.00	5.400	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-16	21	C
8.00	7.000	115/230	AC	TransGlobal International (PC Mount)		TG56-16	23	C
8.00	10.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-16	21	C
8.00	16.200	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-16	21	C
8.00	22.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-16	21	C
9.00	0.100	120	DC	Power Sources (Wall Plug-In)		STA-3590B	13	F
9.00	0.130	230/50HZ	AC	Power Sources (Wall Plug-In)		STAF-0437F	17	C
9.00	0.200	120	DC	Power Sources (Wall Plug-In)		STA-3590	13	G
9.00	0.200	120	DC	Power Sources (Wall Plug-In)		STA-4190C	13	G
9.00	0.200	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-2223F	17	C
9.00	0.300	120	DC	Power Sources (Wall Plug-In)		STA-4175A	13	F
9.00	0.300	120	AC	Power Sources (Wall Plug-In)		STA-4190B	13	G
9.00	0.300	120	DC	Power Sources (Wall Plug-In)		STA-3590A	13	G
9.00	0.300	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-3309F	17	C
9.00	0.400	120	DC	Power Sources (Wall Plug-In)		STA-4890B	13	H
9.00	0.500	120	AC	Power Sources (Wall Plug-In)		STA-4190D	13	H
9.00	0.500	120	DC	Power Sources (Wall Plug-In)		STA-4190A	13	H
9.00	0.500	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-1058F	17	C
9.00	0.700	120	DC	Power Sources (Wall Plug-In)		STA-4190F	13	H
9.00	0.750	115	AC	Power Transformers		P-8690	48	G
9.00	1.000	115	AC	Power Transformers		P-8691	48	G
9.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4890	13	I
9.00	1.000	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-0329F	17	D
9.00	1.200	120	DC	Power Sources (Wall Plug-In)		STA-4890A	13	I
9.00	1.200	120	DC	Power Sources (Wall Plug-In)		STA-4890A-4	13	I
9.00	1.500	115	AC	Power Transformers		P-8692	48	H
9.00	2.000	115	AC	Power Transformers		P-8693	48	H
9.00	3.000	120	DC	Power Sources (Desk-Top)		STA-6690	13	I
9.00	3.400	120	AC	Power Sources (Desk-Top)		STA-5790	13	I
10.00	0.050	115/230	AC	Power Transformers		P-8500	48	H
10.00	0.055	115	AC	Printed Circuit Transformers		SW-220	29	D
10.00	0.055	115/230	AC	Printed Circuit Transformers		DSW-220	29	D
10.00	0.110	115	AC	Printed Circuit Transformers	*	SW-210	29	A
10.00	0.110	115	AC	Printed Circuit Transformers		SW-220	29	D
10.00	0.110	115/230	AC	Printed Circuit Transformers	*	DSW-210	29	A
10.00	0.110	115/230	AC	Printed Circuit Transformers		DSW-220	29	D
10.00	0.120	115	AC	Printed Circuit Transformers		SW-320	29	D
10.00	0.120	115/230	AC	Printed Circuit Transformers		DSW-320	29	D
10.00	0.200	115/230	AC	Printed Circuit Transformers	*	LB-210	27	A
10.00	0.200	115/230	AC	Printed Circuit Transformers		LB-420	27	D
10.00	0.225	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-28	33	C
10.00	0.240	115	AC	Printed Circuit Transformers		SW-320	29	D
10.00	0.240	115/230	AC	Printed Circuit Transformers		DSW-320	29	D



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
10.00	0.240	115/230	AC	TransGlobal International (PC Mount)		TG2H-20	23	D
10.00	0.250	115	AC	Printed Circuit Transformers	*	SW-310	29	A
10.00	0.250	115/230	AC	Printed Circuit Transformers		LB-520	27	D
10.00	0.250	115/230	AC	Printed Circuit Transformers	*	DSW-310	29	A
10.00	0.250	115/230	AC	Power Transformers		P-8504	48	H
10.00	0.250	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-10	23	A
10.00	0.300	115	AC	Printed Circuit Transformers		SW-420	29	D
10.00	0.300	115/230	AC	Printed Circuit Transformers	*	LB-310	27	A
10.00	0.300	115/230	AC	Printed Circuit Transformers		LB-620	27	E
10.00	0.300	115/230	AC	Printed Circuit Transformers		DSW-420	29	D
10.00	0.300	115/230	AC	Power Transformers		P-8505	48	I
10.00	0.300	120	DC	Power Sources (Wall Plug-In)		STA-4110A	14	A
10.00	0.400	115/230	AC	Printed Circuit Transformers	*	LB-410	27	A
10.00	0.400	115/230	AC	Printed Circuit Transformers		LB-420	27	D
10.00	0.450	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-28	33	C
10.00	0.500	115/230	AC	Printed Circuit Transformers	*	LB-510	27	A
10.00	0.500	115/230	AC	Printed Circuit Transformers		LB-520	27	D
10.00	0.500	115/230	AC	Power Transformers		P-8507	48	I
10.00	0.500	115/230	AC	TransGlobal International (PC Mount)	*	TG05-10	23	A
10.00	0.500	115/230	AC	TransGlobal International (PC Mount)		TG05-20	23	D
10.00	0.600	115	AC	Printed Circuit Transformers	*	SW-410	29	A
10.00	0.600	115	AC	Printed Circuit Transformers		SW-420	29	D
10.00	0.600	115/230	AC	Printed Circuit Transformers	*	LB-610	27	B
10.00	0.600	115/230	AC	Printed Circuit Transformers		LB-1220	27	E
10.00	0.600	115/230	AC	Printed Circuit Transformers		LB-620	27	E
10.00	0.600	115/230	AC	Printed Circuit Transformers	*	DSW-410	29	A
10.00	0.600	115/230	AC	Printed Circuit Transformers		DSW-420	29	D
10.00	0.600	115/230	AC	Printed Circuit Transformers		DSW-520	29	D
10.00	0.600	115/230	AC	Printed Circuit Transformers		DSW-520	29	D
10.00	0.700	120	AC	Power Sources (Wall Plug-In)		STA-4110	14	A
10.00	1.000	115	AC	Printed Circuit Transformers		SW-620	29	D
10.00	1.000	115/230	AC	Printed Circuit Transformers		DSW-620	29	D
10.00	1.000	115/230	AC	Power Transformers		P-8508	48	I
10.00	1.000	115/230	AC	TransGlobal International (PC Mount)	*	TG10-10	23	A
10.00	1.000	115/230	AC	TransGlobal International (PC Mount)		TG10-20	23	D
10.00	1.000	117	AC	Power Transformers	*	P-8652	47	F
10.00	1.000	117	AC	Power Transformers		P-8604	49	A
10.00	1.200	115	AC	Printed Circuit Transformers	*	SW-510	29	A
10.00	1.200	115/230	AC	Printed Circuit Transformers	*	LB-1210	27	B
10.00	1.200	115/230	AC	Printed Circuit Transformers		LB-1220	27	E
10.00	1.200	115/230	AC	Printed Circuit Transformers	*	DSW-510	29	A
10.00	1.200	115/230	AC	Printed Circuit Transformers		DSW-520	29	D
10.00	1.200	115/230	AC	Printed Circuit Transformers		DSW-520	29	D
10.00	1.200	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-57	33	E
10.00	2.000	115	AC	Printed Circuit Transformers	*	SW-610	29	A
10.00	2.000	115	AC	Printed Circuit Transformers		SW-620	29	D
10.00	2.000	115	AC	Power Transformers		P-8559	49	A
10.00	2.000	115/230	AC	Printed Circuit Transformers	*	DSW-610	29	A
10.00	2.000	115/230	AC	Printed Circuit Transformers		DSW-620	29	D



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
10.00	2.000	115/230	AC	TransGlobal International (PC Mount)	*	TG20-10	23	A
10.00	2.000	115/230	AC	TransGlobal International (PC Mount)		TG20-20	23	D
10.00	2.000	117	AC	Power Transformers	*	P-8653	47	G
10.00	2.400	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-57	33	E
10.00	2.500	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-10	21	A
10.00	2.500	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-20	21	D
10.00	3.000	115/230	AC	TransGlobal International (PC Mount)	*	TG30-10	23	A
10.00	3.000	115/230	AC	TransGlobal International (PC Mount)		TG30-20	23	D
10.00	3.000	117	AC	Power Transformers	*	P-8380	47	G
10.00	4.000	115	AC	Power Transformers		P-8560	49	A
10.00	4.000	117	AC	Power Transformers	*	P-5016	47	G
10.00	4.000	117	AC	Power Transformers	*	P-8654	47	G
10.00	4.300	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-10	21	A
10.00	4.400	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-20	21	D
10.00	5.000	117/107	AC	Power Transformers	*	P-6458	47	G
10.00	5.600	115/230	AC	TransGlobal International (PC Mount)	*	TG56-10	23	A
10.00	5.600	115/230	AC	TransGlobal International (PC Mount)		TG56-20	23	D
10.00	6.000	117	AC	Power Transformers	*	P-8655	48	A
10.00	8.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-10	21	A
10.00	8.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-20	21	D
10.00	8.000	117	AC	Power Transformers	*	P-8656	48	A
10.00	10.000	117	AC	Power Transformers	*	P-6461	48	A
10.00	13.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-10	21	A
10.00	13.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-20	21	D
10.00	17.500	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-10	21	A
10.00	17.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-20	21	D
12.00	0.045	115	AC	Printed Circuit Transformers		SW-224	30	A
12.00	0.045	115/230	AC	Printed Circuit Transformers		DSW-224	30	A
12.00	0.050	120	DC	Power Sources (Wall Plug-In)		STA-3512	14	A
12.00	0.085	117	AC	Power Transformers		P-8394	49	B
12.00	0.085	230	AC	Power Transformers		P-8720	49	B
12.00	0.090	115	AC	Printed Circuit Transformers		SW-224	30	A
12.00	0.090	115/230	AC	Printed Circuit Transformers		DSW-224	30	A
12.00	0.100	115	AC	Printed Circuit Transformers		SW-324	30	A
12.00	0.100	115/230	AC	Printed Circuit Transformers		DSW-324	30	A
12.00	0.100	117	AC	Power Transformers (Multiple Secondary)	*	P-8361	52	A
12.00	0.100	120	DC	Power Sources (Wall Plug-In)		STA-3512C	14	A
12.00	0.100	120	AC	Power Sources (Wall Plug-In)		STA-3512E	14	B
12.00	0.150	117	AC	Power Transformers		P-8390	48	A
12.00	0.150	117	AC	Power Transformers (Multiple Secondary)	*	P-8362	52	B
12.00	0.167	115/230	AC	Printed Circuit Transformers		LB-424	27	E
12.00	0.180	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-20	33	D
12.00	0.200	115	AC	Printed Circuit Transformers		SW-324	30	A
12.00	0.200	115/230	AC	Printed Circuit Transformers		DSW-324	30	A
12.00	0.200	115/230	AC	Power Transformers		P-8578	49	C
12.00	0.200	115/230	AC	TransGlobal International (PC Mount)		TG2H-24	23	E
12.00	0.200	117	AC	Power Transformers		P-8395	49	B
12.00	0.200	120	AC	Power Sources (Wall Plug-In)		STA-3512F	14	B
12.00	0.200	120	DC	Power Sources (Wall Plug-In)		STA-300R	14	B



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
12.00	0.200	120	DC	Power Sources (Wall Plug-In)		STA-3512B	14	B
12.00	0.200	120	DC	Power Sources (Desk-Top)		STAR-9005	15	C
12.00	0.200	120	DC	Power Sources (Desk-Top)		STAR-9006	15	C
12.00	0.200	230	AC	Power Transformers		P-8721	49	C
12.00	0.208	115/230	AC	Printed Circuit Transformers		LB-524	27	E
12.00	0.250	115	AC	Printed Circuit Transformers		SW-424	30	A
12.00	0.250	115/230	AC	Printed Circuit Transformers		LB-624	27	F
12.00	0.250	115/230	AC	Printed Circuit Transformers		DSW-424	30	A
12.00	0.300	120	DC	Power Sources (Wall Plug-In)		STA-4112B	14	C
12.00	0.300	120	DC	Power Sources (Desk-Top)		STAR-9007	15	C
12.00	0.300	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-3382F	17	D
12.00	0.330	115/230	AC	Printed Circuit Transformers	*	LB-412	27	B
12.00	0.333	115/230	AC	Printed Circuit Transformers		LB-424	27	E
12.00	0.350	117	AC	Power Transformers		P-8391	48	B
12.00	0.360	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-20	33	D
12.00	0.400	117	AC	Power Transformers		P-8396	49	C
12.00	0.400	120	DC	Power Sources (Wall Plug-In)		STA-4112	14	C
12.00	0.400	230	AC	Power Transformers		P-8722	49	C
12.00	0.417	115/230	AC	Printed Circuit Transformers	*	LB-512	27	B
12.00	0.417	115/230	AC	Printed Circuit Transformers		LB-524	27	E
12.00	0.420	115/230	AC	TransGlobal International (PC Mount)		TG05-24	23	E
12.00	0.500	115	AC	Printed Circuit Transformers		SW-424	30	A
12.00	0.500	115	AC	Printed Circuit Transformers		SW-524	30	A
12.00	0.500	115/230	AC	Printed Circuit Transformers		LB-1224	27	F
12.00	0.500	115/230	AC	Printed Circuit Transformers		LB-624	27	F
12.00	0.500	115/230	AC	Printed Circuit Transformers		DSW-424	30	A
12.00	0.500	115/230	AC	Printed Circuit Transformers		DSW-524	30	A
12.00	0.500	117	AC	Power Transformers (Multiple Secondary)	*	P-8364	52	B
12.00	0.500	120	AC	Power Sources (Wall Plug-In)		STA-4112A	14	C
12.00	0.500	120	DC	Power Sources (Wall Plug-In)		STA-4112C	14	C
12.00	0.500	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-2343F	17	D
12.00	0.600	120	DC	Power Sources (Wall Plug-In)		STA-4812D	14	D
12.00	0.700	117	AC	Power Transformers		P-8392	48	B
12.00	0.700	117	AC	Power Transformers		P-8397	49	D
12.00	0.700	230	AC	Power Transformers		P-8723	49	D
12.00	0.800	115	AC	Printed Circuit Transformers		SW-624	30	A
12.00	0.800	115/230	AC	Printed Circuit Transformers		DSW-624	30	A
12.00	0.840	115/230	AC	TransGlobal International (PC Mount)		TG10-24	23	E
12.00	0.850	120	AC	Power Sources (Wall Plug-In)		STA-4812B	14	D
12.00	1.000	115	AC	Printed Circuit Transformers		SW-524	30	A
12.00	1.000	115	AC	Power Transformers (Dual Secondary)	*	P-8683	51	B
12.00	1.000	115/230	AC	Printed Circuit Transformers		LB-1224	27	F
12.00	1.000	115/230	AC	Printed Circuit Transformers		DSW-524	30	A
12.00	1.000	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-58	33	E
12.00	1.000	115/230	AC	Power Transformers		P-8575	49	D
12.00	1.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6375	52	C
12.00	1.000	117	AC	Power Transformers		P-8661	49	D
12.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4812A	14	D
12.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-4812A-4	14	D



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
12.00	1.000	120	DC	Power Sources (Desk-Top)		STAR-9003	15	C
12.00	1.000	230/50HZ	DC	Power Sources (Desk-Top)		STAF-1454FD	17	D
12.00	1.200	117	AC	Power Transformers		P-8393	48	B
12.00	1.200	120	DC	Power Sources (Wall Plug-In)		STA-5712	14	E
12.00	1.200	120	DC	Power Sources (Wall Plug-In)		STA-5712-4	14	E
12.00	1.200	120	DC	Power Sources (Desk-Top)		STAR-9004	15	C
12.00	1.200	230/50HZ	DC	Power Sources (Desk-Top)		STAF-1948FD	17	D
12.00	1.600	115	AC	Printed Circuit Transformers		SW-624	30	A
12.00	1.600	115/230	AC	Printed Circuit Transformers		DSW-624	30	A
12.00	1.660	115/230	AC	TransGlobal International (PC Mount)		TG20-24	23	E
12.00	2.000	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-58	33	E
12.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6376	52	C
12.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6377	52	C
12.00	2.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-24	21	E
12.00	2.000	117	AC	Power Transformers		P-8657	48	B
12.00	2.000	117	AC	Power Transformers		P-8662	49	E
12.00	2.000	120	DC	Power Sources (Desk-Top)		STA-6612	14	E
12.00	2.500	115/230	AC	TransGlobal International (PC Mount)		TG30-24	23	E
12.00	2.500	120	DC	Power Sources (Desk-Top)		STA-6612A	14	E
12.00	3.000	120	DC	Power Sources (Desk-Top)		STA-6612B	14	F
12.00	3.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-24	21	E
12.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6377	52	C
12.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6378	52	C
12.00	4.000	117	AC	Power Transformers		P-8658	48	C
12.00	4.000	117	AC	Power Transformers		P-8663	49	E
12.00	4.660	115/230	AC	TransGlobal International (PC Mount)		TG56-24	23	E
12.00	6.000	117	AC	Power Transformers		P-8659	48	C
12.00	6.000	117	AC	Power Transformers		P-8664	49	E
12.00	6.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-24	21	E
12.00	8.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6378	52	C
12.00	8.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6379	52	C
12.00	8.000	117	AC	Power Transformers		P-8660	48	C
12.00	8.000	117	AC	Power Transformers		P-8665	49	E
12.00	10.000	115	AC	Power Transformers		P-8695	49	F
12.00	10.800	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-24	21	E
12.00	12.000	117	AC	Power Transformers		P-8666	49	F
12.00	14.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-24	21	E
12.00	16.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6379	52	C
12.25	0.250	117	AC	Power Transformers		P-8607	49	H
12.50	0.800	120	DC	Power Sources (Wall Plug-In)		STA-4812	14	F
12.60	0.090	115	AC	Printed Circuit Transformers	*	SW-212	29	B
12.60	0.090	115/230	AC	Printed Circuit Transformers	*	DSW-212	29	B
12.60	0.200	115	AC	Printed Circuit Transformers	*	SW-312	29	B
12.60	0.200	115/230	AC	Printed Circuit Transformers	*	DSW-312	29	B
12.60	0.200	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-12	23	B
12.60	0.350	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-18	33	C
12.60	0.400	115/230	AC	TransGlobal International (PC Mount)	*	TG05-12	23	B
12.60	0.450	115/230	AC	Printed Circuit Transformers	*	LB-612	27	C
12.60	0.500	115	AC	Printed Circuit Transformers	*	SW-412	29	B



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
12.60	0.500	115/230	AC	Printed Circuit Transformers	*	DSW-412	29	B
12.60	0.800	115/230	AC	TransGlobal International (PC Mount)	*	TG10-12	23	B
12.60	0.800	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-0460F	17	E
12.60	0.900	115/230	AC	Printed Circuit Transformers	*	LB-1212	27	C
12.60	1.000	115	AC	Printed Circuit Transformers	*	SW-512	29	B
12.60	1.000	115/230	AC	Printed Circuit Transformers	*	DSW-512	29	B
12.60	1.000	117	AC	Power Transformers	*	P-8384	48	C
12.60	1.000	117	AC	Power Transformers		P-8180	49	G
12.60	1.500	117	AC	Power Transformers	*	P-8550	48	D
12.60	1.600	115	AC	Printed Circuit Transformers	*	SW-612	31	B
12.60	1.600	115/230	AC	Printed Circuit Transformers	*	DSW-612	29	B
12.60	1.600	115/230	AC	TransGlobal International (PC Mount)	*	TG20-12	23	B
12.60	2.000	115/230	AC	Power Transformers		P-8574	49	G
12.60	2.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-12	21	B
12.60	2.000	117	AC	Power Transformers	*	P-8130	48	D
12.60	2.000	117	AC	Power Transformers		P-8357	49	G
12.60	2.000	230	AC	Power Transformers	*	P-8715	48	D
12.60	2.400	115/230	AC	TransGlobal International (PC Mount)	*	TG30-12	23	B
12.60	2.800	117	AC	Power Transformers		P-8388	49	G
12.60	3.000	117	AC	Power Transformers	*	P-8358	48	D
12.60	3.400	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-12	21	B
12.60	4.000	117	AC	Power Transformers	*	P-8641	48	E
12.60	4.000	230	AC	Power Transformers	*	P-8716	48	E
12.60	4.400	115/230	AC	TransGlobal International (PC Mount)	*	TG56-12	23	B
12.60	5.000	117	AC	Power Transformers		P-8645	49	H
12.60	6.000	117	AC	Power Transformers	*	P-8642	48	E
12.60	6.300	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-12	21	B
12.60	10.000	117	AC	Power Transformers	*	P-8644	48	E
12.60	10.300	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-12	21	B
12.60	14.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-12	21	B
13.00	0.250	117	AC	Power Transformers		P-8607	49	H
13.40	1.000	117	AC	Power Transformers		P-8609	49	H
13.50	1.300	120	DC	Power Sources (Wall Plug-In)		STA-5713	14	F
13.50	1.300	230/50HZ	DC	Power Sources (Desk-Top)		STAF-1059FD	17	E
13.50	1.700	120	DC	Power Sources (Wall Plug-In)		STA-5713A	14	F
13.50	1.700	120	DC	Power Sources (Desk-Top)		STA-5713AC	14	G
13.50	1.700	230/50HZ	DC	Power Sources (Desk-Top)		STAF-2134F	17	E
13.50	2.100	120	DC	Power Sources (Desk-Top)		STA-6013A	14	G
13.50	2.100	230/50HZ	DC	Power Sources (Desk-Top)		STAF-3775F	17	E
13.50	2.400	120	DC	Power Sources (Desk-Top)		STA-6613	14	G
13.50	2.400	230/50HZ	DC	Power Sources (Desk-Top)		STAF-3777F	17	E
13.75	0.250	117	AC	Power Transformers		P-8607	49	H
14.00	0.040	115	AC	Printed Circuit Transformers		SW-228	30	B
14.00	0.040	115/230	AC	Printed Circuit Transformers		DSW-228	30	B
14.00	0.080	115	AC	Printed Circuit Transformers		SW-228	30	B
14.00	0.080	115/230	AC	Printed Circuit Transformers		DSW-228	30	B
14.00	0.085	115	AC	Printed Circuit Transformers		SW-328	30	B
14.00	0.085	117	AC	Power Transformers		P-8600	49	H
14.00	0.170	115	AC	Printed Circuit Transformers		SW-328	30	B



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
14.00	0.170	115/230	AC	Printed Circuit Transformers		DSW-328	30	B
14.00	0.175	117	AC	Power Transformers		P-8601	49	I
14.00	0.180	115/230	AC	TransGlobal International (PC Mount)		TG2H-28	23	F
14.00	0.200	115	AC	Printed Circuit Transformers		SW-428	30	B
14.00	0.200	115/230	AC	Printed Circuit Transformers		DSW-428	30	B
14.00	0.250	115	AC	Power Transformers	*	P-8553	48	F
14.00	0.250	115/230	AC	Power Transformers	*	P-8577	48	F
14.00	0.300	117	AC	Power Transformers		P-8602	49	I
14.00	0.360	115/230	AC	TransGlobal International (PC Mount)		TG05-28	23	F
14.00	0.400	115	AC	Printed Circuit Transformers		SW-428	30	B
14.00	0.400	115/230	AC	Printed Circuit Transformers		DSW-428	30	B
14.00	0.420	115	AC	Printed Circuit Transformers		SW-528	30	B
14.00	0.420	115/230	AC	Printed Circuit Transformers		DSW-528	30	B
14.00	0.700	115	AC	Printed Circuit Transformers		SW-628	30	B
14.00	0.700	115/230	AC	Printed Circuit Transformers		DSW-628	30	B
14.00	0.720	115/230	AC	TransGlobal International (PC Mount)		TG10-28	23	F
14.00	0.800	117	AC	Power Transformers		P-8603	49	I
14.00	0.840	115	AC	Printed Circuit Transformers		SW-528	30	B
14.00	0.840	115/230	AC	Printed Circuit Transformers		DSW-528	30	B
14.00	0.850	115/230	AC	Printed Circuit Transformers		DSW-328	30	B
14.00	1.000	115	AC	Power Transformers	*	P-8555	48	F
14.00	1.000	117	AC	Power Transformers		P-8667	50	A
14.00	1.400	115	AC	Printed Circuit Transformers		SW-628	30	B
14.00	1.400	115/230	AC	Printed Circuit Transformers		DSW-628	30	B
14.00	1.400	230/50HZ	DC	Power Sources (Desk-Top)		STAF-3613F	17	F
14.00	1.440	115/230	AC	TransGlobal International (PC Mount)		TG20-28	23	F
14.00	1.800	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-28	21	F
14.00	2.000	115	AC	Power Transformers	*	P-8556	48	F
14.00	2.000	117	AC	Power Transformers		P-8668	50	A
14.00	2.120	115/230	AC	TransGlobal International (PC Mount)		TG30-28	23	F
14.00	3.000	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-28	21	F
14.00	4.000	115	AC	Power Transformers	*	P-8557	48	G
14.00	4.000	115/230	AC	TransGlobal International (PC Mount)		TG56-28	23	F
14.00	4.000	117	AC	Power Transformers		P-8669	50	A
14.00	5.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-28	21	F
14.00	6.000	115	AC	Power Transformers	*	P-8558	48	G
14.00	6.000	117	AC	Power Transformers		P-8670	50	A
14.00	9.200	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-28	21	F
14.00	12.500	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-28	21	F
14.50	0.250	117	AC	Power Transformers		P-8607	49	H
14.50	0.800	120	DC	Power Sources (Wall Plug-In)		STA-4814	14	G
14.50	0.800	230/50HZ	DC	Power Sources (Wall Plug-In)		STAF-0354F	17	F
15.00	0.050	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-3	33	A
15.00	0.050	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-8	33	A
15.00	0.100	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-2	33	A
15.00	0.100	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-3	33	A
15.00	0.100	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-46	33	A
15.00	0.100	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-8	33	A
15.00	0.150	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-13	33	D



White-Rodgers • Emerson Electric Co.
9797 Reavis Road • St. Louis, MO 63123
(314) 865-8799 • Fax (314) 638-2400



STANCOR 117

QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
15.00	0.150	115/230	AC	Printed Circuit Transformers	*	LB-215	27	C
15.00	0.150	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-48	33	D
15.00	0.225	115/230	AC	Printed Circuit Transformers	*	LB-315	27	C
15.00	0.250	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-23	33	E
15.00	0.300	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-13	33	D
15.00	0.300	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-12	33	C
15.00	0.300	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-47	33	C
15.00	0.300	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-48	33	D
15.00	0.500	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-22	33	E
15.00	0.500	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-23	33	E
15.00	0.600	120	DC	Power Sources (Wall Plug-In)		STA-4815	14	G
15.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-5715	14	H
15.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-5715-4	14	H
15.00	1.000	230/50HZ	DC	Power Sources (Desk-Top)		STAF-1972F	17	F
15.00	2.000	120	DC	Power Sources (Desk-Top)		STA-6615	14	H
15.50	0.750	115	AC	Power Transformers (Dual Secondary)	*	P-8750	51	B
16.00	0.035	115	AC	Printed Circuit Transformers		SW-232	30	C
16.00	0.035	115/230	AC	Printed Circuit Transformers		DSW-232	30	C
16.00	0.070	115	AC	Printed Circuit Transformers	*	SW-216	29	C
16.00	0.070	115	AC	Printed Circuit Transformers		SW-232	30	C
16.00	0.070	115/230	AC	Printed Circuit Transformers	*	DSW-216	29	C
16.00	0.070	115/230	AC	Printed Circuit Transformers		DSW-232	30	C
16.00	0.075	115	AC	Printed Circuit Transformers		SW-332	30	C
16.00	0.075	115/230	AC	Printed Circuit Transformers		DSW-332	30	C
16.00	0.150	115	AC	Printed Circuit Transformers	*	SW-316	29	C
16.00	0.150	115	AC	Printed Circuit Transformers		SW-332	30	C
16.00	0.150	115/230	AC	Printed Circuit Transformers	*	DSW-316	29	C
16.00	0.150	115/230	AC	Printed Circuit Transformers		DSW-332	30	C
16.00	0.150	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-16	23	C
16.00	0.188	115	AC	Printed Circuit Transformers		SW-432	30	C
16.00	0.188	115/230	AC	Printed Circuit Transformers		DSW-432	30	C
16.00	0.250	120	AC	Power Sources (Wall Plug-In)		STA-4116	14	H
16.00	0.280	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-19	33	C
16.00	0.310	115/230	AC	TransGlobal International (PC Mount)	*	TG05-16	23	C
16.00	0.350	115/230	AC	Printed Circuit Transformers	*	LB-616	27	D
16.00	0.375	115	AC	Printed Circuit Transformers		SW-532	30	C
16.00	0.375	115/230	AC	Printed Circuit Transformers		DSW-532	30	C
16.00	0.376	115	AC	Printed Circuit Transformers		SW-432	30	C
16.00	0.376	115/230	AC	Printed Circuit Transformers		DSW-432	30	C
16.00	0.400	115	AC	Printed Circuit Transformers	*	SW-416	29	C
16.00	0.400	115/230	AC	Printed Circuit Transformers	*	DSW-416	29	C
16.00	0.620	115/230	AC	TransGlobal International (PC Mount)	*	TG10-16	23	C
16.00	0.625	115	AC	Printed Circuit Transformers		SW-632	30	C
16.00	0.625	115/230	AC	Printed Circuit Transformers		DSW-632	30	C
16.00	0.700	115/230	AC	Printed Circuit Transformers	*	LB-1216	27	D
16.00	0.750	115	AC	Printed Circuit Transformers		SW-532	30	C
16.00	0.750	115/230	AC	Printed Circuit Transformers		DSW-532	30	C
16.00	0.800	115	AC	Printed Circuit Transformers	*	SW-516	29	C
16.00	0.800	115/230	AC	Printed Circuit Transformers	*	DSW-516	29	C



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
16.00	1.250	115	AC	Printed Circuit Transformers	*	SW-616	29	C
16.00	1.250	115	AC	Printed Circuit Transformers		SW-632	30	C
16.00	1.250	115/230	AC	Printed Circuit Transformers	*	DSW-616	29	C
16.00	1.250	115/230	AC	Printed Circuit Transformers		DSW-632	30	C
16.00	1.250	115/230	AC	TransGlobal International (PC Mount)	*	TG20-16	23	C
16.00	1.500	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-56	33	E
16.00	1.600	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-16	21	C
16.00	1.900	115/230	AC	TransGlobal International (PC Mount)	*	TG30-16	23	C
16.00	2.700	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-16	21	C
16.00	3.500	115/230	AC	TransGlobal International (PC Mount)	*	TG56-16	23	C
16.00	5.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-16	21	C
16.00	8.100	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-16	21	C
16.00	11.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-16	21	C
17.00	0.170	115/230	AC	Printed Circuit Transformers		LB-634	27	F
17.00	0.340	115/230	AC	Printed Circuit Transformers		LB-1234	27	F
17.00	0.340	115/230	AC	Printed Circuit Transformers		LB-634	27	F
17.00	0.680	115/230	AC	Printed Circuit Transformers		LB-1234	27	F
18.00	0.030	115	AC	Printed Circuit Transformers		SW-236	30	D
18.00	0.030	115/230	AC	Printed Circuit Transformers		DSW-236	30	D
18.00	0.060	115	AC	Printed Circuit Transformers		SW-236	30	D
18.00	0.060	115/230	AC	Printed Circuit Transformers		DSW-236	30	D
18.00	0.065	115	AC	Printed Circuit Transformers		SW-336	30	D
18.00	0.065	115/230	AC	Printed Circuit Transformers		DSW-336	30	D
18.00	0.065	117	AC	Power Transformers		P-8610	50	B
18.00	0.130	115	AC	Printed Circuit Transformers		SW-336	30	D
18.00	0.130	115/230	AC	Printed Circuit Transformers		DSW-336	30	D
18.00	0.135	117	AC	Power Transformers		P-8611	50	B
18.00	0.140	115/230	AC	TransGlobal International (PC Mount)		TG2H-36	24	A
18.00	0.170	115	AC	Printed Circuit Transformers		SW-436	30	D
18.00	0.170	115/230	AC	Printed Circuit Transformers		DSW-436	30	D
18.00	0.280	115/230	AC	TransGlobal International (PC Mount)		TG05-36	24	A
18.00	0.300	117	AC	Power Transformers		P-8612	50	B
18.00	0.300	120	AC	Power Sources (Wall Plug-In)		STA-4118	14	H
18.00	0.340	115	AC	Printed Circuit Transformers		SW-436	30	D
18.00	0.340	115/230	AC	Printed Circuit Transformers		DSW-436	30	D
18.00	0.350	115	AC	Printed Circuit Transformers		SW-536	30	D
18.00	0.350	115/230	AC	Printed Circuit Transformers		DSW-536	30	D
18.00	0.550	115	AC	Printed Circuit Transformers		SW-636	30	D
18.00	0.550	115/230	AC	Printed Circuit Transformers		DSW-636	30	D
18.00	0.550	117	AC	Power Transformers		P-8613	50	B
18.00	0.560	115/230	AC	TransGlobal International (PC Mount)		TG10-36	24	A
18.00	0.700	115	AC	Printed Circuit Transformers		SW-536	30	D
18.00	0.700	115/230	AC	Printed Circuit Transformers		DSW-536	30	D
18.00	0.750	115	AC	Power Transformers	*	P-8690	48	G
18.00	1.000	115	AC	Power Transformers	*	P-8691	48	G
18.00	1.000	115	AC	Power Transformers (Dual Secondary)	*	P-8684	51	B
18.00	1.000	117	AC	Power Transformers		P-8671	50	C
18.00	1.100	115	AC	Printed Circuit Transformers		SW-636	30	D
18.00	1.100	115/230	AC	Printed Circuit Transformers		DSW-636	30	D



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
18.00	1.120	115/230	AC	TransGlobal International (PC Mount)		TG20-36	24	A
18.00	1.250	117	AC	Power Transformers (Dual Secondary)	*	PCA-3	51	A
18.00	1.400	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-36	21	G
18.00	1.500	115	AC	Power Transformers	*	P-8692	48	H
18.00	1.640	115/230	AC	TransGlobal International (PC Mount)		TG30-36	24	A
18.00	2.000	115	AC	Power Transformers	*	P-8693	48	H
18.00	2.000	115	AC	Power Transformers (Dual Secondary)	*	P-8685	51	B
18.00	2.000	117	AC	Power Transformers		P-8672	50	C
18.00	2.000	120	DC	Power Sources (Desk-Top)		STA-6618	15	I
18.00	2.000	120	DC	Power Sources (Desk-Top)		STA-6618-4	15	I
18.00	2.400	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-36	21	G
18.00	3.120	115/230	AC	TransGlobal International (PC Mount)		TG56-36	24	A
18.00	4.000	117	AC	Power Transformers		P-8673	50	C
18.00	4.400	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-36	21	G
18.00	6.000	117	AC	Power Transformers		P-8674	50	C
18.00	7.200	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-36	21	G
18.00	9.600	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-36	21	G
18.50	0.080	120	DC	Power Sources (Wall Plug-In)		STA-3518	14	I
19.00	2.500	117	AC	Power Transformers (Dual Secondary)	*	PCA-4	51	A
20.00	0.038	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-7	33	B
20.00	0.050	115/230	AC	Power Transformers	*	P-8500	48	H
20.00	0.055	115	AC	Printed Circuit Transformers	*	SW-220	29	D
20.00	0.055	115/230	AC	Printed Circuit Transformers	*	DSW-220	29	D
20.00	0.060	115/230	AC	Printed Circuit Transformers		LB-240	27	G
20.00	0.076	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-7	33	B
20.00	0.112	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-17	33	D
20.00	0.120	115	AC	Printed Circuit Transformers	*	SW-320	29	D
20.00	0.120	115/230	AC	Printed Circuit Transformers		LB-240	27	G
20.00	0.120	115/230	AC	Printed Circuit Transformers	*	DSW-320	29	D
20.00	0.120	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-20	23	D
20.00	0.150	115/230	AC	Printed Circuit Transformers		LB-640	27	G
20.00	0.188	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-27	33	E
20.00	0.200	115/230	AC	Printed Circuit Transformers	*	LB-420	27	D
20.00	0.224	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-17	33	D
20.00	0.225	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-28	33	C
20.00	0.250	115/230	AC	Printed Circuit Transformers	*	LB-520	27	D
20.00	0.250	115/230	AC	Power Transformers	*	P-8504	48	H
20.00	0.250	115/230	AC	Power Transformers		P-8542	50	D
20.00	0.250	115/230	AC	TransGlobal International (PC Mount)	*	TG05-20	23	D
20.00	0.280	120	DC	Power Sources (Wall Plug-In)		STA-4120	14	I
20.00	0.300	115	AC	Printed Circuit Transformers	*	SW-420	29	D
20.00	0.300	115/230	AC	Printed Circuit Transformers	*	LB-620	27	E
20.00	0.300	115/230	AC	Printed Circuit Transformers		LB-1240	27	G
20.00	0.300	115/230	AC	Printed Circuit Transformers		LB-640	27	G
20.00	0.300	115/230	AC	Printed Circuit Transformers	*	DSW-420	29	D
20.00	0.300	115/230	AC	Power Transformers	*	P-8505	48	I
20.00	0.376	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-27	33	E
20.00	0.500	115/230	AC	Power Transformers	*	P-8507	48	I
20.00	0.500	115/230	AC	TransGlobal International (PC Mount)	*	TG10-20	23	D



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
20.00	0.600	115/230	AC	Printed Circuit Transformers	*	LB-1220	27	E
20.00	0.600	115/230	AC	Printed Circuit Transformers		LB-1240	27	G
20.00	0.600	115/230	AC	Printed Circuit Transformers	*	DSW-520	29	D
20.00	0.700	120	AC	Power Sources (Wall Plug-In)		STA-4820	14	D
20.00	1.000	115	AC	Printed Circuit Transformers	*	SW-620	29	D
20.00	1.000	115	AC	Power Transformers		P-8564	50	D
20.00	1.000	115/230	AC	Printed Circuit Transformers	*	DSW-620	29	D
20.00	1.000	115/230	AC	Power Transformers	*	P-8508	48	I
20.00	1.000	115/230	AC	TransGlobal International (PC Mount)	*	TG20-20	23	D
20.00	1.000	117	AC	Power Transformers	*	P-8604	49	A
20.00	1.200	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-57	33	E
20.00	1.250	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-20	21	D
20.00	1.500	115/230	AC	TransGlobal International (PC Mount)	*	TG30-20	23	D
20.00	2.000	115	AC	Power Transformers	*	P-8559	49	A
20.00	2.200	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-20	21	D
20.00	2.800	115/230	AC	TransGlobal International (PC Mount)	*	TG56-20	23	D
20.00	4.000	115	AC	Power Transformers	*	P-8560	49	A
20.00	4.000	115	AC	Power Transformers		P-8566	50	D
20.00	4.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-20	21	D
20.00	6.500	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-20	21	D
20.00	8.800	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-20	21	D
24.00	0.023	115	AC	Printed Circuit Transformers		SW-248	31	A
24.00	0.023	115/230	AC	Printed Circuit Transformers		DSW-248	31	A
24.00	0.045	115	AC	Printed Circuit Transformers	*	SW-224	30	A
24.00	0.045	115/230	AC	Printed Circuit Transformers	*	DSW-224	30	A
24.00	0.046	115	AC	Printed Circuit Transformers		SW-248	31	A
24.00	0.046	115/230	AC	Printed Circuit Transformers		DSW-248	31	A
24.00	0.050	115	AC	Printed Circuit Transformers		SW-348	31	A
24.00	0.050	115/230	AC	Printed Circuit Transformers		DSW-348	31	A
24.00	0.050	120	DC	Power Sources (Wall Plug-In)		STA-3524	15	A
24.00	0.085	117	AC	Power Transformers	*	P-8394	49	B
24.00	0.085	230	AC	Power Transformers	*	P-8720	49	B
24.00	0.100	115	AC	Printed Circuit Transformers	*	SW-324	30	A
24.00	0.100	115	AC	Printed Circuit Transformers		SW-348	31	A
24.00	0.100	115/230	AC	Printed Circuit Transformers	*	DSW-324	30	A
24.00	0.100	115/230	AC	Printed Circuit Transformers		DSW-348	31	A
24.00	0.100	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-24	23	E
24.00	0.125	115	AC	Printed Circuit Transformers		SW-448	31	A
24.00	0.125	115/230	AC	Printed Circuit Transformers		DSW-448	31	A
24.00	0.167	115/230	AC	Printed Circuit Transformers	*	LB-424	27	E
24.00	0.180	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-20	33	D
24.00	0.200	115/230	AC	Power Transformers	*	P-8578	49	C
24.00	0.200	117	AC	Power Transformers	*	P-8395	49	B
24.00	0.200	230	AC	Power Transformers	*	P-8721	49	C
24.00	0.208	115/230	AC	Printed Circuit Transformers	*	LB-524	27	E
24.00	0.210	115/230	AC	TransGlobal International (PC Mount)	*	TG05-24	23	E
24.00	0.250	115	AC	Printed Circuit Transformers	*	SW-424	30	A
24.00	0.250	115	AC	Printed Circuit Transformers		SW-448	31	A



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
24.00	0.250	115	AC	Printed Circuit Transformers		SW-548	31	A
24.00	0.250	115/230	AC	Printed Circuit Transformers	*	LB-624	27	F
24.00	0.250	115/230	AC	Printed Circuit Transformers	*	DSW-424	30	A
24.00	0.250	115/230	AC	Printed Circuit Transformers		DSW-448	31	A
24.00	0.250	115/230	AC	Printed Circuit Transformers		DSW-548	31	A
24.00	0.250	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8615	52	D
24.00	0.300	120	AC	Power Sources (Wall Plug-In)		STA-4124	15	A
24.00	0.400	115	AC	Printed Circuit Transformers		SW-648	31	A
24.00	0.400	115/230	AC	Printed Circuit Transformers		DSW-648	31	A
24.00	0.400	117	AC	Power Transformers	*	P-8396	49	C
24.00	0.400	230	AC	Power Transformers	*	P-8722	49	C
24.00	0.400	230/50HZ	AC	Power Sources (Wall Plug-In)		STAF-2098F	17	F
24.00	0.420	115/230	AC	TransGlobal International (PC Mount)	*	TG10-24	23	E
24.00	0.450	120	AC	Power Sources (Wall Plug-In)		STA-4824B	15	A
24.00	0.500	115	AC	Printed Circuit Transformers	*	SW-524	30	A
24.00	0.500	115	AC	Printed Circuit Transformers		SW-548	31	A
24.00	0.500	115/230	AC	Printed Circuit Transformers	*	LB-1224	27	F
24.00	0.500	115/230	AC	Printed Circuit Transformers	*	DSW-524	30	A
24.00	0.500	115/230	AC	Printed Circuit Transformers		DSW-548	31	A
24.00	0.500	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8615	52	D
24.00	0.500	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8616	52	D
24.00	0.600	120	DC	Power Sources (Wall Plug-In)		STA-4824AT	15	B
24.00	0.700	117	AC	Power Transformers	*	P-8397	49	D
24.00	0.700	230	AC	Power Transformers	*	P-8723	49	D
24.00	0.800	115	AC	Printed Circuit Transformers	*	SW-624	30	A
24.00	0.800	115	AC	Printed Circuit Transformers		SW-648	31	A
24.00	0.800	115/230	AC	Printed Circuit Transformers	*	DSW-624	30	A
24.00	0.800	115/230	AC	Printed Circuit Transformers		DSW-648	31	A
24.00	0.830	115/230	AC	TransGlobal International (PC Mount)	*	TG20-24	23	E
24.00	1.000	115	AC	Power Transformers		P-8551	49	A
24.00	1.000	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-58	33	E
24.00	1.000	115/230	AC	Power Transformers	*	P-8575	49	D
24.00	1.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8616	52	D
24.00	1.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8617	52	D
24.00	1.000	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-24	21	E
24.00	1.000	117	AC	Power Transformers	*	P-8661	49	D
24.00	1.000	117	AC	Power Transformers		P-8605	50	D
24.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-5724AT	15	B
24.00	1.000	120	DC	Power Sources (Wall Plug-In)		STA-5724AT-4	15	B
24.00	1.250	115/230	AC	TransGlobal International (PC Mount)	*	TG30-24	23	E
24.00	1.500	120	DC	Power Sources (Desk-Top)		STA-6624	15	B
24.00	1.670	120	AC	Energy Limiting Transformers		592-9012	65	A
24.00	1.670	120/208/240	AC	Energy Limiting Transformers		592-9018	65	A
24.00	1.670	120/240	AC	Energy Limiting Transformers		592-9016	65	A
24.00	1.670	208/240	AC	Energy Limiting Transformers		592-9017	65	A
24.00	1.670	240	AC	Energy Limiting Transformers		592-9013	65	A
24.00	1.800	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-24	21	E
24.00	2.000	115	AC	Power Transformers		P-8694	49	B
24.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6377	52	C



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
24.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8617	52	D
24.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8618	52	D
24.00	2.000	117	AC	Power Transformers	*	P-8662	49	E
24.00	2.330	115/230	AC	TransGlobal International (PC Mount)	*	TG56-24	23	E
24.00	3.300	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-24	21	E
24.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6378	52	C
24.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8618	52	D
24.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8619	52	D
24.00	4.000	117	AC	Power Transformers	*	P-8663	49	E
24.00	5.400	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-24	21	E
24.00	6.000	117	AC	Power Transformers	*	P-8664	49	E
24.00	7.300	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-24	21	E
24.00	8.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-6379	52	C
24.00	8.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8619	52	D
24.00	8.000	117	AC	Power Transformers	*	P-8665	49	E
24.00	10.000	115	AC	Power Transformers	*	P-8695	49	F
24.00	12.000	117	AC	Power Transformers	*	P-8666	49	F
24.50	0.250	117	AC	Power Transformers	*	P-8607	49	H
25.20	1.000	117	AC	Power Transformers		P-6469	49	F
25.20	1.000	117	AC	Power Transformers	*	P-8180	49	G
25.20	1.000	230	AC	Power Transformers		P-8707	49	F
25.20	2.000	115/230	AC	Power Transformers	*	P-8574	49	G
25.20	2.000	117	AC	Power Transformers	*	P-8357	49	G
25.20	2.800	117	AC	Power Transformers	*	P-8388	49	G
25.20	5.000	117	AC	Power Transformers	*	P-8645	49	H
26.00	0.250	117	AC	Power Transformers	*	P-8607	49	H
26.80	1.000	117	AC	Power Transformers	*	P-8609	49	H
27.00	0.028	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-4	33	B
27.00	0.056	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-4	33	B
27.00	0.084	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-14	33	D
27.00	0.168	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-14	33	D
27.50	0.250	117	AC	Power Transformers	*	P-8607	49	H
28.00	0.020	115	AC	Printed Circuit Transformers		SW-256	31	B
28.00	0.020	115/230	AC	Printed Circuit Transformers		DSW-256	31	B
28.00	0.040	115	AC	Printed Circuit Transformers	*	SW-228	30	B
28.00	0.040	115	AC	Printed Circuit Transformers		SW-256	31	B
28.00	0.040	115/230	AC	Printed Circuit Transformers	*	DSW-228	30	B
28.00	0.040	115/230	AC	Printed Circuit Transformers		DSW-256	31	B
28.00	0.045	115	AC	Printed Circuit Transformers		SW-356	31	B
28.00	0.045	115/230	AC	Printed Circuit Transformers		LB-256	27	G
28.00	0.045	115/230	AC	Printed Circuit Transformers		DSW-356	31	B
28.00	0.085	115	AC	Printed Circuit Transformers	*	SW-328	30	B
28.00	0.085	115/230	AC	Printed Circuit Transformers	*	DSW-328	30	B
28.00	0.085	117	AC	Power Transformers	*	P-8600	49	H
28.00	0.090	115	AC	Printed Circuit Transformers		SW-356	31	B
28.00	0.090	115/230	AC	Printed Circuit Transformers		LB-256	27	G
28.00	0.090	115/230	AC	Printed Circuit Transformers		DSW-356	31	B
28.00	0.090	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-28	23	F
28.00	0.100	115/230	AC	Printed Circuit Transformers		LB-656	27	H



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
28.00	0.110	115	AC	Printed Circuit Transformers		SW-456	31	B
28.00	0.110	115/230	AC	Printed Circuit Transformers		DSW-456	31	B
28.00	0.175	117	AC	Power Transformers	*	P-8601	49	I
28.00	0.180	115/230	AC	TransGlobal International (PC Mount)	*	TG05-28	23	F
28.00	0.200	115	AC	Printed Circuit Transformers	*	SW-428	30	B
28.00	0.200	115/230	AC	Printed Circuit Transformers		LB-1256	27	H
28.00	0.200	115/230	AC	Printed Circuit Transformers		LB-656	27	H
28.00	0.200	115/230	AC	Printed Circuit Transformers	*	DSW-428	30	B
28.00	0.220	115	AC	Printed Circuit Transformers		SW-456	31	B
28.00	0.220	115	AC	Printed Circuit Transformers		SW-556	31	B
28.00	0.220	115/230	AC	Printed Circuit Transformers		DSW-456	31	B
28.00	0.220	115/230	AC	Printed Circuit Transformers		DSW-556	31	B
28.00	0.300	117	AC	Power Transformers	*	P-8602	49	I
28.00	0.350	115	AC	Printed Circuit Transformers		SW-656	31	B
28.00	0.350	115/230	AC	Printed Circuit Transformers		DSW-656	31	B
28.00	0.360	115/230	AC	TransGlobal International (PC Mount)	*	TG10-28	23	F
28.00	0.400	115/230	AC	Printed Circuit Transformers		LB-1256	27	H
28.00	0.420	115	AC	Printed Circuit Transformers	*	SW-528	30	B
28.00	0.420	115/230	AC	Printed Circuit Transformers	*	DSW-528	30	B
28.00	0.440	115	AC	Printed Circuit Transformers		SW-556	31	B
28.00	0.440	115/230	AC	Printed Circuit Transformers		DSW-556	31	B
28.00	0.700	115	AC	Printed Circuit Transformers	*	SW-628	30	B
28.00	0.700	115	AC	Printed Circuit Transformers		SW-656	31	B
28.00	0.700	115/230	AC	Printed Circuit Transformers	*	DSW-628	30	B
28.00	0.700	115/230	AC	Printed Circuit Transformers		DSW-656	31	B
28.00	0.720	115/230	AC	TransGlobal International (PC Mount)	*	TG20-28	23	F
28.00	0.800	117	AC	Power Transformers	*	P-8603	49	I
28.00	0.900	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-28	21	F
28.00	1.000	117	AC	Power Transformers	*	P-8667	50	A
28.00	1.060	115/230	AC	TransGlobal International (PC Mount)	*	TG30-28	23	F
28.00	1.500	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-28	21	F
28.00	2.000	115/230	AC	TransGlobal International (PC Mount)	*	TG56-28	23	F
28.00	2.000	117	AC	Power Transformers	*	P-8668	50	A
28.00	2.800	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-28	21	F
28.00	4.000	117	AC	Power Transformers	*	P-8669	50	A
28.00	4.600	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-28	21	F
28.00	6.000	117	AC	Power Transformers	*	P-8670	50	A
28.00	6.250	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-28	21	F
29.00	0.250	117	AC	Power Transformers	*	P-8607	49	H
30.00	0.050	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-3	33	A
30.00	0.050	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-8	33	A
30.00	0.150	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-13	33	D
30.00	0.150	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-48	33	D
30.00	0.250	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-23	33	E
32.00	0.035	115	AC	Printed Circuit Transformers	*	SW-232	30	C
32.00	0.035	115/230	AC	Printed Circuit Transformers	*	DSW-232	30	C
32.00	0.075	115	AC	Printed Circuit Transformers	*	SW-332	30	C
32.00	0.075	115/230	AC	Printed Circuit Transformers	*	DSW-332	30	C
32.00	0.188	115	AC	Printed Circuit Transformers	*	SW-432	30	C



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
32.00	0.188	115/230	AC	Printed Circuit Transformers	*	DSW-432	30	C
32.00	0.250	115	AC	Power Transformers (Dual Secondary)	*	P-8750	51	B
32.00	0.375	115	AC	Printed Circuit Transformers	*	SW-532	30	C
32.00	0.375	115/230	AC	Printed Circuit Transformers	*	DSW-532	30	C
32.00	0.625	115	AC	Printed Circuit Transformers	*	SW-632	30	C
32.00	0.625	115/230	AC	Printed Circuit Transformers	*	DSW-632	30	C
33.00	0.210	117	AC	Power Transformers (Dual Secondary)	*	PCA-3	51	A
34.00	0.170	115/230	AC	Printed Circuit Transformers	*	LB-634	27	F
34.00	0.340	115/230	AC	Printed Circuit Transformers	*	LB-1234	27	F
34.00	0.350	117	AC	Power Transformers (Dual Secondary)	*	PCA-4	51	A
36.00	0.030	115	AC	Printed Circuit Transformers	*	SW-236	30	D
36.00	0.030	115/230	AC	Printed Circuit Transformers	*	DSW-236	30	D
36.00	0.065	115	AC	Printed Circuit Transformers	*	SW-336	30	D
36.00	0.065	115/230	AC	Printed Circuit Transformers	*	DSW-336	30	D
36.00	0.065	117	AC	Power Transformers	*	P-8610	50	B
36.00	0.070	115/230	AC	TransGlobal International (PC Mount)	*	TG2H-36	24	A
36.00	0.135	117	AC	Power Transformers	*	P-8611	50	B
36.00	0.140	115/230	AC	TransGlobal International (PC Mount)	*	TG05-36	24	A
36.00	0.170	115	AC	Printed Circuit Transformers	*	SW-436	30	D
36.00	0.170	115/230	AC	Printed Circuit Transformers	*	DSW-436	30	D
36.00	0.280	115/230	AC	TransGlobal International (PC Mount)	*	TG10-36	24	A
36.00	0.300	117	AC	Power Transformers	*	P-8612	50	B
36.00	0.350	115	AC	Printed Circuit Transformers	*	SW-536	30	D
36.00	0.350	115/230	AC	Printed Circuit Transformers	*	DSW-536	30	D
36.00	0.550	115	AC	Printed Circuit Transformers	*	SW-636	30	D
36.00	0.550	115/230	AC	Printed Circuit Transformers	*	DSW-636	30	D
36.00	0.550	117	AC	Power Transformers	*	P-8613	50	B
36.00	0.560	115/230	AC	TransGlobal International (PC Mount)	*	TG20-36	24	A
36.00	0.700	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-36	21	G
36.00	0.820	115/230	AC	TransGlobal International (PC Mount)	*	TG30-36	24	A
36.00	1.000	117	AC	Power Transformers	*	P-8671	50	C
36.00	1.200	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-36	21	G
36.00	1.560	115/230	AC	TransGlobal International (PC Mount)	*	TG56-36	24	A
36.00	2.000	117	AC	Power Transformers	*	P-8672	50	C
36.00	2.200	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-36	21	G
36.00	3.600	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-36	21	G
36.00	4.000	117	AC	Power Transformers	*	P-8673	50	C
36.00	4.800	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-36	21	G
36.00	6.000	117	AC	Power Transformers	*	P-8674	50	C
40.00	0.038	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-7	33	B
40.00	0.060	115/230	AC	Printed Circuit Transformers	*	LB-240	27	G
40.00	0.112	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-17	33	D
40.00	0.150	115/230	AC	Printed Circuit Transformers	*	LB-640	27	G
40.00	0.188	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-27	33	E
40.00	0.250	115/230	AC	Power Transformers	*	P-8542	50	D
40.00	0.300	115/230	AC	Printed Circuit Transformers	*	LB-1240	27	G
40.00	1.000	115	AC	Power Transformers	*	P-8564	50	D
40.00	4.000	115	AC	Power Transformers	*	P-8566	50	D
44.00	0.028	115/230	AC	Printed Circuit Transformers		LB-288	27	H



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
44.00	0.056	115/230	AC	Printed Circuit Transformers		LB-288	27	H
44.00	0.065	115/230	AC	Printed Circuit Transformers		LB-688	27	H
44.00	0.130	115/230	AC	Printed Circuit Transformers		LB-688	27	H
44.00	0.130	115/230	AC	Printed Circuit Transformers		LB-1288	27	I
44.00	0.260	115/230	AC	Printed Circuit Transformers		LB-1288	27	I
48.00	0.023	115	AC	Printed Circuit Transformers	*	SW-248	31	A
48.00	0.023	115/230	AC	Printed Circuit Transformers	*	DSW-248	31	A
48.00	0.050	115	AC	Printed Circuit Transformers	*	SW-348	31	A
48.00	0.050	115/230	AC	Printed Circuit Transformers	*	DSW-348	31	A
48.00	0.125	115	AC	Printed Circuit Transformers	*	SW-448	31	A
48.00	0.125	115/230	AC	Printed Circuit Transformers	*	DSW-448	31	A
48.00	0.250	115	AC	Printed Circuit Transformers	*	SW-548	31	A
48.00	0.250	115/230	AC	Printed Circuit Transformers	*	DSW-548	31	A
48.00	0.250	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8615	52	D
48.00	0.400	115	AC	Printed Circuit Transformers	*	SW-648	31	A
48.00	0.400	115/230	AC	Printed Circuit Transformers	*	DSW-648	31	A
48.00	0.500	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8616	52	D
48.00	1.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8617	52	D
48.00	1.000	117	AC	Power Transformers	*	P-8605	50	D
48.00	2.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8618	52	D
48.00	4.000	115/230	AC	Power Transformers (Dual Pri./Sec.)		P-8619	52	D
54.00	0.028	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-4	33	B
54.00	0.084	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-14	33	D
56.00	0.020	115	AC	Printed Circuit Transformers	*	SW-256	31	B
56.00	0.020	115/230	AC	Printed Circuit Transformers	*	DSW-256	31	B
56.00	0.045	115	AC	Printed Circuit Transformers	*	SW-356	31	B
56.00	0.045	115/230	AC	Printed Circuit Transformers	*	LB-256	27	G
56.00	0.045	115/230	AC	Printed Circuit Transformers	*	DSW-356	31	B
56.00	0.100	115/230	AC	Printed Circuit Transformers	*	LB-656	27	H
56.00	0.110	115	AC	Printed Circuit Transformers	*	SW-456	31	B
56.00	0.110	115/230	AC	Printed Circuit Transformers	*	DSW-456	31	B
56.00	0.200	115/230	AC	Printed Circuit Transformers	*	LB-1256	27	H
56.00	0.220	115	AC	Printed Circuit Transformers	*	SW-556	31	B
56.00	0.220	115/230	AC	Printed Circuit Transformers	*	DSW-556	31	B
56.00	0.350	115	AC	Printed Circuit Transformers	*	SW-656	31	B
56.00	0.350	115/230	AC	Printed Circuit Transformers	*	DSW-656	31	B
58.00	0.013	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-6	33	B
58.00	0.026	115	AC	Printed Circuit Transformers (Plug-In Series)		PPC-6	33	B
60.00	0.010	115	AC	Printed Circuit Transformers		SW-2120	31	C
60.00	0.010	115/230	AC	Printed Circuit Transformers		DSW-2120	31	C
60.00	0.020	115	AC	Printed Circuit Transformers		SW-2120	31	C
60.00	0.020	115	AC	Printed Circuit Transformers		SW-3120	31	C
60.00	0.020	115/230	AC	Printed Circuit Transformers		LB-2120	27	I
60.00	0.020	115/230	AC	Printed Circuit Transformers		DSW-2120	31	C
60.00	0.020	115/230	AC	Printed Circuit Transformers		DSW-3120	31	C
60.00	0.033	115/230	AC	Printed Circuit Transformers		LB-4120	27	I
60.00	0.040	115/230	AC	Printed Circuit Transformers		LB-2120	27	I
60.00	0.040	115/230	AC	Printed Circuit Transformers		DSW-3120	31	C
60.00	0.042	115/230	AC	Printed Circuit Transformers		LB-5120	27	I
60.00	0.050	115	AC	Printed Circuit Transformers		SW-4120	31	C



Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
60.00	0.050	115/230	AC	Printed Circuit Transformers		LB-6120	27	J
60.00	0.050	115/230	AC	Printed Circuit Transformers		DSW-4120	31	C
60.00	0.066	115/230	AC	Printed Circuit Transformers		LB-4120	27	I
60.00	0.083	115/230	AC	Printed Circuit Transformers		LB-5120	27	I
60.00	0.100	115	AC	Printed Circuit Transformers		SW-4120	31	C
60.00	0.100	115	AC	Printed Circuit Transformers		SW-5120	31	C
60.00	0.100	115/230	AC	Printed Circuit Transformers		LB-12120	27	J
60.00	0.100	115/230	AC	Printed Circuit Transformers		LB-6120	27	J
60.00	0.100	115/230	AC	Printed Circuit Transformers		DSW-4120	31	C
60.00	0.100	115/230	AC	Printed Circuit Transformers		DSW-5120	31	C
60.00	0.160	115	AC	Printed Circuit Transformers		SW-6120	31	C
60.00	0.160	115/230	AC	Printed Circuit Transformers		DSW-6120	31	C
60.00	0.200	115	AC	Printed Circuit Transformers		SW-5120	31	C
60.00	0.200	115/230	AC	Printed Circuit Transformers		LB-12120	27	J
60.00	0.200	115/230	AC	Printed Circuit Transformers		DSW-5120	31	C
60.00	0.320	115	AC	Printed Circuit Transformers		SW-6120	31	C
60.00	0.320	115/230	AC	Printed Circuit Transformers		DSW-6120	31	C
60.00	0.400	115	AC	Printed Circuit Transformers		SW-3120	31	C
88.00	0.028	115/230	AC	Printed Circuit Transformers	*	LB-288	27	H
88.00	0.065	115/230	AC	Printed Circuit Transformers	*	LB-688	27	H
88.00	0.130	115/230	AC	Printed Circuit Transformers	*	LB-1288	27	I
115.00	0.005	115	AC	Auto / Isolation Transformers		P-6413	69	E
115.00	0.007	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-51	33	B
115.00	0.010	115/230	AC	Printed Circuit Transformers		LB-2230	27	J
115.00	0.013	115/230	AC	Printed Circuit Transformers (Plug-In Series)		PPC-51	33	B
115.00	0.020	115/230	AC	Printed Circuit Transformers		LB-2230	27	J
115.00	0.025	115/230	AC	Printed Circuit Transformers		LB-6230	27	J
115.00	0.050	115/230	AC	Printed Circuit Transformers		LB-12230	27	J
115.00	0.050	115/230	AC	Printed Circuit Transformers		LB-6230	27	J
115.00	0.100	115/230	AC	Printed Circuit Transformers		LB-12230	27	J
115.00	0.130	115	AC	Auto / Isolation Transformers		P-6411	69	E
115.00	0.220	115/230	AC	TransGlobal International (Chassis Mount)		TGC25-230	21	H
115.00	0.300	115	AC	Auto / Isolation Transformers		P-6412	69	E
115.00	0.350	230	AC	Auto / Isolation Transformer		P-6287	69	A
115.00	0.380	115/230	AC	TransGlobal International (Chassis Mount)		TGC43-230	21	H
115.00	0.430	115	AC	Auto / Isolation Transformers		P-6410	69	E
115.00	0.430	115/230	AC	Auto / Isolation Transformers		P-6406	69	F
115.00	0.430	230	AC	Auto / Isolation Transformers		P-8620	69	A
115.00	0.650	115	AC	Auto / Isolation Transformers		P-8622	69	F
115.00	0.650	230	AC	Auto / Isolation Transformers		GSD-75	69	A
115.00	0.650	230/460	AC	Power Transformers		PCF-24075	50	D
115.00	0.700	115/230	AC	TransGlobal International (Chassis Mount)		TGC80-230	21	H
115.00	0.740	230	AC	Auto / Isolation Transformers		P-8630	69	A
115.00	0.870	115	AC	Auto / Isolation Transformers		GIS-100	69	G
115.00	0.870	230	AC	Auto / Isolation Transformers		GSD-100	69	A
115.00	0.870	230	AC	Auto / Isolation Transformers		GISD-100	69	H
115.00	1.100	230	AC	Auto / Isolation Transformers		P-8631	69	B
115.00	1.140	115/230	AC	TransGlobal International (Chassis Mount)		TGC130-230	21	H
115.00	1.300	115	AC	Auto / Isolation Transformers	*	P-8622	69	F
115.00	1.300	115	AC	Auto / Isolation Transformers		GIS-150	69	G



QUICK SELECTION GUIDE

Transformer and Power Supplies

Output Voltage	Output Amps	Input Voltage (AC)	Output AC/DC	Catalog Section (transformer type)	C.T.	STANCOR Part No.	Pg.	Sec.
115.00	1.300	230	AC	Auto / Isolation Transformers		GSD-150	69	B
115.00	1.300	230	AC	Auto / Isolation Transformers		GISD-150	69	H
115.00	1.520	115/230	AC	TransGlobal International (Chassis Mount)		TGC175-230	21	H
115.00	1.740	230	AC	Auto / Isolation Transformers		P-8632	69	B
115.00	2.170	115	AC	Auto / Isolation Transformers		GIS-250	69	G
115.00	2.170	230	AC	Auto / Isolation Transformers		GISD-250	69	H
115.00	2.200	230	AC	Auto / Isolation Transformers		GSD-250	69	B
115.00	2.600	230	AC	Auto / Isolation Transformers		GSD-300	69	B
115.00	3.000	230	AC	Auto / Isolation Transformers		GSD-350	69	C
115.00	3.500	230	AC	Auto / Isolation Transformers		P-8634	69	C
115.00	4.300	230	AC	Auto / Isolation Transformers		GSD-500	69	C
115.00	4.350	115	AC	Auto / Isolation Transformers		GIS-500	69	G
115.00	4.350	230	AC	Auto / Isolation Transformers		GISD-500	69	H
115.00	6.500	230	AC	Auto / Isolation Transformers		GSD-750	69	C
115.00	8.700	115	AC	Auto / Isolation Transformers		GIS-1000	69	G
115.00	8.700	230	AC	Auto / Isolation Transformers		GSD-1000	69	C
115.00	8.700	230	AC	Auto / Isolation Transformers		GISD-1000	69	H
115.00	13.000	230	AC	Auto / Isolation Transformers		GSD-1500	69	D
116.00	0.013	115	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-6	33	B
120.00	0.010	115	AC	Printed Circuit Transformers	*	SW-2120	31	C
120.00	0.010	115/230	AC	Printed Circuit Transformers	*	DSW-2120	31	C
120.00	0.020	115	AC	Printed Circuit Transformers	*	SW-3120	31	C
120.00	0.020	115/230	AC	Printed Circuit Transformers	*	LB-2120	27	I
120.00	0.020	115/230	AC	Printed Circuit Transformers	*	DSW-3120	31	C
120.00	0.033	115/230	AC	Printed Circuit Transformers	*	LB-4120	27	I
120.00	0.042	115/230	AC	Printed Circuit Transformers	*	LB-5120	27	I
120.00	0.050	115	AC	Printed Circuit Transformers	*	SW-4120	31	C
120.00	0.050	115/230	AC	Printed Circuit Transformers	*	LB-6120	27	J
120.00	0.050	115/230	AC	Printed Circuit Transformers	*	DSW-4120	31	C
120.00	0.100	115	AC	Printed Circuit Transformers	*	SW-5120	31	C
120.00	0.100	115/230	AC	Printed Circuit Transformers	*	LB-12120	27	J
120.00	0.100	115/230	AC	Printed Circuit Transformers	*	DSW-5120	31	C
120.00	0.160	115	AC	Printed Circuit Transformers	*	SW-6120	31	C
120.00	0.160	115/230	AC	Printed Circuit Transformers	*	DSW-6120	31	C
230.00	0.007	115/230	AC	Printed Circuit Transformers (Plug-In Series)	*	PPC-51	33	B
230.00	0.010	115/230	AC	Printed Circuit Transformers	*	LB-2230	27	J
230.00	0.025	115/230	AC	Printed Circuit Transformers	*	LB-6230	27	J
230.00	0.050	115/230	AC	Printed Circuit Transformers	*	LB-12230	27	J
230.00	0.110	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC25-230	21	H
230.00	0.190	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC43-230	21	H
230.00	0.350	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC80-230	21	H
230.00	0.370	115	AC	Auto / Isolation Transformers		P-8637	69	D
230.00	0.540	115	AC	Auto / Isolation Transformers		P-8638	69	D
230.00	0.570	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC130-230	21	H
230.00	0.650	115	AC	Auto / Isolation Transformers		P-8622	69	F
230.00	0.760	115/230	AC	TransGlobal International (Chassis Mount)	*	TGC175-230	21	H
230.00	1.300	115	AC	Auto / Isolation Transformers		P-8639	69	D
230.00	2.170	115	AC	Auto / Isolation Transformers		P-8640	69	D
230.00	4.350	115	AC	Auto / Isolation Transformers		P-8689	69	E

