





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
266	2.5	.350	.200	2.51	20,000	C-2R
253	2.5	.350	LENS	END	20,000	C-2R
FG23	5.0	.020	.020	0.25	50,000	C-2R
3152	5.0	.060	.150	1.89	5,000	C-2R
7348	5.0	.115	.150	1.89	40,000	C-2R
8705	6.0	.040	.030	0.38	10,000	C-2V
337	6.0	.200	.630	7.92	1,000	C-2R
7351	6.3	.040	.030	0.38	20,000	C-2V
8708	6.3	.075	.230	2.89	1,000	C-2R
379	6.3	.200	.400	5.03	50,000	C-2F
398	6.3	.200	.550	6.91	5,000	C-2R
709	10.0	.014	.004	0.05	50,000	C-2F
397	10.0	.040	.080	1.01	30,000	C-2F
7354	12.0	.040	.120	1.51	10,000	C-2F
386	14.0	.080	.300	3.77	50,000	C-2F
336	14.0	.080	.500	6.29	2,500	C-2F
346	18.0	.040	.150	1.89	10,000	C-2F
7355	28.0	.040	.200	2.51	50,000	C-2F
388	28.0	.040	.300	3.77	25,000	C-2F
334	28.0	.040	.340	4.27	4,000	C-2F
7356	28.0	.065	.650	8.17	5,000	C-2F



DIMENSIONS ARE IN MILLIMETERS
TOLERANCE UNLESS OTHERWISE SPECIFIED
1 PL +/- 0.2
2 PL +/- 0.20
ANGLE +/- 0

JKL COMPONENTS CORPORATION

TITLE

T-1 3/4 STANDARD MIDGET GROOVE

DRAWN BY
L. WENGSTROM

APPVD BY DATE
J.K. 8/2/05

SIZE
A

FSCM NO.
55335

DRAWING NO.

GROOVE BASE T-1 3/4

- CAD DRAWING -
MANUAL REVISIONS NOT PERMITTED

SCALE

NONE

RELEASED DATE
10/11/00

REVISION DATE
8/2/05

REV. NO. A

SHEET 1 OF 1

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
A	DELETED PART #'S 393, 457, 276 RELEASE & CANCEL 7346, 7347	8/2/050 10/11/00