




REV	DESCRIPTION	DET	DATE
C	REWROTE NOTES. ADDED .453 CENTER TO EDGE DIMENSION	MK	11/13/09
D	128514C WAS 128624C. ADDED 128488	JJC	07/31/12

- NOTES:
- 1 MAXIMUM RECOMMENDED STROKE: .500.
 - 2 FOR USE WITH 206-375 TOOL, FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SALES SPECIALIST.
 - 3 SHIP WITH: STOP 126747 AND DEFLECTOR 126748-1.
 - 4 128624C ASSEMBLY CONSISTS OF 128514C COLLET AND 128488 DRAWBAR.
 - 5 127134C ASSEMBLY CONSISTS OF 127078C ANVIL HOLDER AND 120309 ANVIL INSERT.

D	128488	1	DRAWBAR	9
	126748-1	1	UNITIZED DEFLECTOR	8
D	128514C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	122912	1	BARBED RETAINER	4
	128073	1	UNITIZED CHUCK JAW	3
	127582	1	TOP GUARD	2
	127134C	1	ANVIL ASSEMBLY	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:	HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401		
ECCN: EAR99	CLEARANCE NOSE ASSEMBLY -10 ASP LONG		
SCH B#: 8467.99.0190	DET: MVM	CK:	DATE: 10/13/04 SCALE: 2:1
HTS: 8467.99.0190	B	99-3730-1C	