


THIS DOCUMENT CONTAINS DATA PROPRIETARY  
TO PROJECTS UNLIMITED, INC. ANY USE OR  
REPRODUCTION, IN ANY FORM, WITHOUT PRIOR  
WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC.  
IS PROHIBITED.  
© 2005, Projects Unlimited Inc.

## SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.1	W
MAX INPUT POWER	0.1	W
IMPEDANCE	8±15%	OHM
OUTPUT SPL @ 1W/0.1M (AT 0.8, 1.0, 1.2, 1.5 kHz)	93±3	dBA
DISTORTION (MAX.)	5%	—
RESONANT FREQUENCY	600±20%	Hz
FREQUENCY RANGE	600 ~ 5400	Hz
HOUSING MATERIAL	METAL	—
CONE MATERIAL	PAPER	—
MAGNET MATERIAL	COBALT	—
OPERATING TEMPERATURE	-20 ~ +60	°C
WEIGHT	11.3	grams




### NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE  
OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME  
AT-40008.DWG

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	05/07/02	
A	REVISED TO NEW TEMPLATE	12/28/05	B.R.



UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN  
MILLIMETERS, TOLERANCES ARE ±0.5 AND  
ANGLES ARE ±3°.

APPROVALS	DATE
DRAWN RABL	05/02
CHECKED X.X.	X/XX
APPROVED S.J.	05/07/02

DO NOT SCALE DRAWING

projects ®  
unlimited

Dayton, Ohio

SPEAKER

SIZE A DRAWING NO.  
AT-40008

SCALE: N.T.S. SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AT-40008](#)