




CRYSTEK
MICROWAVE
A DIVISION OF CRYSTEK CORPORATION

RG58A/U N-TYPE RF COAX CABLE ASSEMBLIES



RG58A/U 50 ohms
N-Type Coaxial Cable Assemblies



Features:

Strain Relief: Adhesive shrink tubing over crimp area
Center Conductor: TPC (Tin-Plated Copper) 19/0072
Shielding: TPC (Tin-Plated Copper) 96% Coverage, Single Braid
Dielectric: Solid Polyethylene
Jacket: PVC (Polyvinyl Chloride) Black
Operating Temperature: -40°C to +80°C
Minimum Bend Radius: 1.0"

Part Number	Description	Length
CCN-MM-RG58-12	RG58A/U Shielded Cable, N-Type Male/Male	12"
CCN-MM-RG58-24	RG58A/U Shielded Cable, N-Type Male/Male	24"
CCN-MM-RG58-36	RG58A/U Shielded Cable, N-Type Male/Male	36"