



English | 简体中文 | 日本語

Search by Part Number

GO

Search Site by keyword

GO

Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > > 452 > 452M-19LFT

You may also like...

452M-19LFT

Category:

Generic Part:

452

Market Group:

MICROCLOCK

Description:

CLOCK SYNTHESIZER

Time is
money

Parameters

Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	No
Minimum Order Quantity	2500
Factory Order Increment	2500

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Package	SOIC 8 (DCG8)
Description	SOIC 150 ML
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	M
Package Type	SOIC
Lead Count	8
Length	4.9 mm
Width	3.9 mm
Thickness	1.5 mm
Pitch	1.27 mm
Tube / Tray	TUBE
Quantity per Tube/Tray	97
Quantity per Reel	2500
Moisture Sensitivity Level (MSL)	1
Moisture Exposure Floor Life	Unlimited@<30C/85% RH
Peak Reflow Temperature	260Â°C
Rebake Conditions	NA
Related Package Documents	view documents

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).