

550-650 W High Wattage Fan Heater *SCR Series*



Features

- For large heating capacity requirements.
- Maintains minimum operating temperatures in enclosures.
- Helps prevent failures to components caused by condensation and corrosion.
- Built-in thermostat and control light.
- Heating power adjusts to ambient temperature.
- Heat exits top of fan heater. (add 2" clearance for heat sensitive parts)

Part No.	Watts	Inrush		Temperature		Ship Wt. lbs
		Current (Amps)	Volts	Maximum with Fan		
SCR027009	550 W	11 A	AC 120	250°F/120°C		2
SCR027009230	550 W	13 A	AC 230	250°F/120°C		2
SCR027019	650 W	12 A	AC 120	320°F/160°C		2.4

Air Flow:	20 CFM (550W), 26 CFM (650W)
Thermostat Range:	32 - 140 degrees Fahrenheit
Heating Element:	PTC - Semiconductor/resistor
Housing:	Plastic, rated UL94-VO
Connection:	3 pole terminal, AWG 14 max (2.5 mm ²)
Mounting:	Clip for 35mm DIN rail
Protection Class:	II (Double Insulated)
Protection Type:	IP20
Approval:	UL Recognized Component, cUL Recognized Component, CE

Data subject to change without notice