

Solutions for
Electronic Specialty
Markets (ESM)

Product Catalog
for Electronic
Specialty Markets

- 3M® Electronic Specialty Markets New Product Releases
- 3M® Abrasives
- 3M® Adhesives, Cleaners & Compounds
- 3M® Breadboards & Test Clips
- 3M® Cable & Assemblies
- 3M® Copper Interconnects
- 3M® Fiber Optics
- 3M® Fire Protection
- 3M® Heat Shrink
- 3M® Identification Systems
- 3M® Occupational Health & Safety Products
- 3M® Protective Bumpers
- 3M® Reclosable Fasteners
- 3M® Splicing, Terminating & Ducting
- 3M® Static Control
- 3M® Tapes
- 3M® Terminals, Kits & Tools
- 3M® Vacuums & Accessories
- 3M® Warehousing & Packaging Supplies
- 3M® Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Search This Product Catalog


By Keyword

Go

[Product Catalog for Electronic Specialty Markets](#) [3M® Terminals, Kits & Tools](#) [Ring Tongues](#)
[Scotchlok® Ring Tongue Terminals](#) - [Vinyl Insulated Brazed Seam](#)

3M® Scotchlok® Vinyl Insulated Brazed Seam Ring Tongue Terminal MV10 -516R/SK, Stud Size 5/16

 [Printer-friendly format](#)



[\[click to
enlarge\]](#)

This terminal has a wire range of 12 - 10 AWG and a stud size of 5/16. It comes in quantities of 500 per case.

GTIN(UPC/EAN) : 0 00 54007 01926 8
3M Id : 80 - 6100 - 4860 - 7

Additional Information

A ring is the standard style of tongue. The safest and most reliable; it cannot be removed unless mounting screw is removed.

Learn More . . .

- [Packaging Data](#)
- [3M® Scotchlok® Terminals MVU18 - 2R/S thru MVU10 - 38R/S - Data Sheet \(PDF 29.7 K\)](#)
- [Ring Tongues - Vinyl Insulated Brazed Seam 12 - 10 AWG - Product Selection Guide \(PDF 21.1 K\)](#)
- [Terminal Stud Size Chart - Product Selection Guide \(PDF 5.2 K\)](#)

Please Note:
Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Agency Approvals	UL and CSA
Barrel Style	Brazed
China RoHS - Below MCV	No
CSA File Number	LR22190
EPC Can View	Public
EU RoHS Compliant	No
Insulation Material	Vinyl
Stud Size	5/16 Inch
Terminal Style	Standard
Terminal Type	Ring
UL File Number	E23438
Wire Gauge Range	10 to 12 American Wire Gauge (AWG)