

Technical Data

Base material	: Polyolefin, cross-linked (POX)
Colour	: see below
Continuous operating temperature	: -55 °C to +135 °C
Shrink temperature	: +100 °C
Longitudinal change	: +/- 5% max.
Shrink ratio	: 3 : 1
Isolation class	: B (VDE 0530)
Accreditation	: SAE-AMS-DTL-23053/5 : UL224 125°C 600V VW-1 (except clear)



	Claimed values	Typical values	Test method
Dielectric strength	: 19,7 kV/mm min.	20 kV/mm	ASTM D 150
Tensile strength	: 10,3 MPa min.	14 MPa	ASTM D 2671
Elongation at break	: 200% min.	800%	ASTM D 2671
Heat aging 168 h/175 °C - Ultimate elongation	: 50 %	≥ 200%	ASTM D 2671
Heat shock 4 h/250 °C	: no cracking, flowing or dripping		ASTM D 2671
Low temperature flexibility 4 h/-55 °C	: no cracking		MIL-DTL-23053
Flammability	: VW-1		UL224
Water absorption	: 0,5% max	0,15%	ASTM D 570

Type designation and technical data

Order no.	Type	As supplied	Fully recovered		Packing content
		Inner diameter mm min.	Inner diameter mm max.	Wall thickness mm nom.	
308-3015_*)	HIS-3-1,5/0,5	1,50	0,50	0,45	10
308-3030_*)	HIS-3-3/1	3,00	1,00	0,55	10
308-3060_*)	HIS-3-6/2	6,00	2,00	0,65	5
308-3090_*)	HIS-3-9/3	9,00	3,00	0,75	5
308-3120_*)	HIS-3-12/4	12,00	4,00	0,80	5
308-3180_*)	HIS-3-18/6	18,00	6,00	0,90	4
308-3240_*)	HIS-3-24/8	24,00	8,00	1,20	3

*) Kennzeichnung der Farbe in der Bestellnummer

Colour	: Black (BK)	Red (RD)	Blue (BU)	Clear (CL)	Green/Yellow (GNYE)*
Order-No.	: 0	2	6	3	7

*Lieferbar ab 3/1

HellermannTyton

HellermannTyton GmbH
Grosser Moorweg 45
D-25436 Tornesch

Telefon: +49 (0) 4122/701-1
Telefax: +49 (0) 4122/701-400

This information is based on our experience and does not imply suitability without prior testing. Due to the variables of manufacture and environmental conditions it is strongly recommended that samples are tested in-situ