


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	REVISED	21FEB2017	D.Z	S.L

- NOTES:
1. MATERIAL:
- 1.1 HOUSING: HIGH TEMPERATURE THERMO PLASTIC,UL94V-0,COLOR:BLACK.
- 1.2 CONTACT: COPPER ALLOY.
- 1.3 SOLDER PEG AND LATCH:STAINLESS STEEL.
2. FINISH:
- SOLDER PEG: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- CONTACT SOLDER AREA: GOLD FLASH ON SOLDERTAIL.
- 2.1 CONTACT AREA: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.2 CONTACT AREA: 5u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.3 CONTACT AREA: 10u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.4 CONTACT AREA: 15U" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
- 2.5 CONTACT AREA: 30U" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
3. COPLANARITY: 0.10 MAX. (BEFORE SOLDERING)






MATING/UNMATING VIEW

SCALE 2:1




MATING: ① INSERTING(25°) → ② ROTATING → ③ FIXED

UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING



TAPE&REEL	BLACK	1.2V	30u"	260	2309413-5
TAPE&REEL	BLACK	1.2V	15u"	260	2309413-4
TAPE&REEL	BLACK	1.2V	10u"	260	2309413-3
TAPE&REEL	BLACK	1.2V	5u"	260	2309413-2
TAPE&REEL	BLACK	1.2V	GF	260	2309413-1
PACKING TYPE	HOUSING COLOR	POWER SUPPLY	FINISH	POS	PART NO.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity		
DIMENSIONS: mm		CHK RICHARD MA 09SEP2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SIMON LI 09SEP2016	NAME		
0 PLC ± -		PRODUCT SPEC	DDR4 SODIMM SOCKET		
1 PLC ± 0.25		108-115122	0.5mm PITCH 260POS		
2 PLC ± 0.15		APPLICATION SPEC	9.2mm HEIGHT STANDARD TYPE		
3 PLC ± 0.10		—	SIZE	CAGE CODE	DRAWING NO
4 PLC ± 0		WEIGHT	A2	00779	C=2309413
ANGLES ± -		CUSTOMER DRAWING	SCALE	1:1	SHEET 1 of 3
FINISH					REV 3



DETAIL:C
SCALE 2:1

DETAIL:D

SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016		 TE Connectivity	
		CHK RICHARD MA 09SEP2016			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± °		NAME DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 9.2mm HEIGHT STANDARD TYPE	
					
MATERIAL		FINISH		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO G-2309413	
				RESTRICTED TO	
		WEIGHT			
		CUSTOMER DRAWING		SCALE 1:1	
				SHEET 2 of 3	
				REV 3	





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	-	-	-	-

D



C

B

A



REEL
TOTAL
2LAYERS



250	2	500	*-2309413-*
PCS/ REEL	REEL/ CARTON	PCS/ CARTON	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity		
DIMENSIONS: mm		CHK RICHARD MA 09SEP2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD SIMON LI 09SEP2016	NAME		
0 PLC ± -		PRODUCT SPEC	DDR4 SODIMM SOCKET		
1 PLC ± -		APPLICATION SPEC	0.5mm PITCH 260POS		
2 PLC ± -		WEIGHT	9.2mm HEIGHT STANDARD TYPE		
3 PLC ± -		CUSTOMER DRAWING	SIZE CAGE CODE DRAWING NO		
4 PLC ± -		SCALE	RESTRICTED TO		
ANGLES ± -		SHEET	REV		
FINISH		3 OF 3	3		