




Specifications:

- Primary voltage: 120V 60Hz 15W
- Exciting current, open circuit: 120mA max.
- DC resistance $\pm 10\%$: 125 Ω
- Secondary, no load voltage: 17.7VDC
- Loaded voltage: 12VDC @ 500mA
- DC resistance $\pm 10\%$: 1 Ω
- Insulation resistance: 100M Ω @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute
primary-core: 1,500VAC for 1 minute
secondary-core: 500VAC for 1 minute
- Temperature rise: 65°C max. @ rated load



File No. E170147

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

412-112059