

(1,27mm) .050"

DWM, HDWM SERIES



HDWM-20-58-G-S-427

HDWM-24-59-L-S-300-SM

DWM-08-56-L-D-312-SM

DWM-06-54-G-D-360

MICRO BOARD STACKER

SPECIFICATIONS

DWM

For complete specifications
see www.samtec.com?DWM

Insulator Material:

Top: Black LCP
Bottom: Natural LCP

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50μ" (1,27μm) Ni

Current Rating:

1A

Operating Temp Range:
55°C to 125°C with Time

-55°C to +105°C V
-55°C to +125°C V

-55
Rol
Yes

HDWM

For complete specifications
see www.samtec.com?HDWM

Same as DWM except
not CSA rated.


Processing:

Processing.

Lead-Free Solderable:

SMT Lead Coplanarity:
(0,15mm) .006" max

Mates with:
SMS, SLM, RSM

Variable
stacker
height

*Ideal for high density
"skyscraper"
board stacking*

Choice of Surface mount or Through-hole

TYPE STRIP

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

ROW OPTION

STACKER HEIGHT

OTHER OPTION

01
thru
50

Specify
LEAD
STYLE
from
chart

—L
= 10μ" (0,25μm)
Gold contact,
Matte Tin
on tail

—G
= 10μ" (0,25μm)
Gold on post,
Gold flash
on tail

—S
= Single
Row

—D
= Double
Row

—"XXX"
= Stacker
Height
Example:
-250 =
(6,35mm)
.250"

—"XXX"
= Polarized
Position
(Specify position
of omitted pin)

DWM
= Standard Board Spacer

HDWM
= High Temp Board Spacer

LEAD STYLE	OAL	
	THROUGH-HOLE	SURFACE MOUNT
—01	(11,43) .450	(8,38) .330
—51	(10,41) .410	—
—52	(10,80) .425	—
—53	(12,83) .505	(9,78) .385
—54	(14,10) .555	(11,05) .435
—55	(15,49) .610	(12,45) .490
—56	(15,88) .625	(12,83) .505
—57	(16,51) .650	(13,46) .530
—58	(17,91) .705	(14,86) .585
—59	(19,18) .755	(15,62) .615
—60	(20,96) .825	—
—61	(26,67) 1.050	—

—SM
= Surface Mount
(Requires HDWM.
02 thru 40
positions only.)

—A
= Alignment Pin
(Requires HDWM.
6 positions min
—D only.)
Metal or plastic at
Samtec discretion
(N/A with —LC)

—LC
= Locking Clip
(Requires HDWM.
5 positions min.
—D only)
(N/A with —A)
(Manual placement
required)

—P
= Pick & Place Pad
(Requires HDWM)

Note: Other Gold plating options available.
Contact Samtec.

Note: These Series are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 **SAMTEC SILICON VALLEY** • Tel: 408-395-5900 **SAMTEC SOUTHERN CALIFORNIA** • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA. • Tel: (+55 31) 3786 3227 **SAMTEC UNITED KINGDOM** • Tel: 44 141 0236 739292 **SAMTEC GERMANY** • Tel: 49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 **SAMTEC ITALY** • Tel: 39 039 6880337 **SAMTEC NORDIC/BALTIC** • Tel: +46-84477280 **SAMTEC BENELUX** • Tel: 44 1236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 **SAMTEC INDIA** • Tel: +91-80-3272 1612 **SAMTEC ASIA PACIFIC** • Tel: 65 6745-5955 **SAMTEC JAPAN** • Tel: 045-475-185 **SAMTEC CHINA** • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 **SAMTEC HONG KONG** • Tel: 852-26904858 **SAMTEC KOREA** • Tel: 82-31-717-5685 **SAMTEC ANZ** • Tel: 613 9580 0683