



Search Results

- Evaluate
- FAQ's
 - Press Releases
 - PANDUIT Fibe ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
- Installation Instructions
 - PDF-Mini-Com FJ ..

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'FJEPGM2.0CEI'

Your search criteria matched only one product, shown below

FJEPGM2.0CEI



- TIA/EIA-604 FOCIS-6 compliant connectors
- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: 0.1dB average (multimode), 0.2dB average (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- RJ45 small form factor duplex plug
- Non-optical disconnect maintains data transmission under tensile loads
- Each duplex plug includes housing, insert, two ferrule assemblies, two crimp sleeves, one boot for 3mm jacketed cable and two dust caps
- Fiber cable type: tight-buffered recommended
- Fiber cable size: 3.0mm jacketed cable or 1.6mm - 2.0mm jacketed cable (noted in part description)
- Ferrule type: 2.5mm zirconia ceramic (highest durability for repeated matings)
- Field polish termination -- *PANDUIT®* recommends anaerobic adhesive
- Use field polish termination kit (FJKITG)

Part Number	FJEPGM2.0CEI
RoHS Compliancy Status	Compliant
Part Description	FJ® Multimode Duplex Fiber Optic Plug for 1.6mm – 2.0mm jacketed cable installation.
Product Type	FJ® Plugs
Color	Electric Ivory
Fiber Compatibility	62.5/125?m / 50/125?m
Fiber Cable Size	1.6mm - 2.0mm or 900?m
Fiber Cable Type	Tight-buffered recommended
Fiber Type	Multimode
Termination Style	Field Polish
Ferrule Type	Zirconia Ceramic
Pricing Description	mm Enhanced FJ Connector
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.