

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100039](#)
Status: **Active**
Description: Pro-Yellow® 32W Fluorescent Benchlight with Molded 16-3 SJTW 8 FT

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Portable Lighting
Series	130110
Depth	N/A
Height	N/A
Length	1.16m (3.80')
NEMA Configuration	NEMA 5-15
Outlet	None
Product Name	Pro-Yellow®
Type	Wide Area Lamps
Woodhead	Yes

Physical	
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	N/A
Duty	Light
Guard Type	N/A
Material - Globe	PVC
Material - Guard	N/A
Mounting Style	Stand
Packaging Type	Carton

Electrical	
Bulb Type	Flourescent
Cord Type - Primary	16/3 SOOW
Lamp Type	F32/T8
Lamp Wattage - Maximum	32W
Lumens	2800
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info	
Old Part Number	HC001-010



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130110Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION