

EMC housing - HC-B 24-TFQ-76/O1STM40G-EMV - 1642823

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://download.phoenixcontact.com>)



HEAVYCON sleeve housing B24, for double locking latch, height 76 mm, with thread M40, straight cable outlet, EMC version



Key commercial data

Packing unit	1 PCE
Weight per Piece (excluding packing)	235.83 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	76 mm
Width	43 mm
Length	120 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 100 °C

General

Note	For contact inserts HC-B24, BB46, D64, DD108, M
Design	B24
Housing type	Sleeve housings
Locking type	For double locking latch
No. of cable exits	1
Cable exit	Straight
Screw connection	None
Type of the screw connection	1x M40

EMC housing - HC-B 24-TFQ-76/O1STM40G-EMV - 1642823

Technical data

General

Housing material	Aluminum die-cast
Housing surface material	EMC coating, silver

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Accessories

Accessories

Full screw connection

Cable gland - HC-EMV-KV-M40(19-28) - 1690545




EMC screw connection up to 5 bar, thread length: 15 mm, cable diameter: 19.0 - 28.0 mm, WAF 45, screw connection: M40

EMC housing - HC-B 24-TFQ-76/O1STM40G-EMV - 1642823

Drawings

Diagram



Dimensioned drawing

