

TIGER EYE™ IDC SOCKET CABLE

(2.00 mm) .0787" PITCH • TCSD SERIES



TCSD

Mates:

TMM, TMMH, STMM,
MMT, TW, MTMM, EHT,
ETMM (-SR), ZSTMM

SPECIFICATIONS

Insulator Material:

Black Glass Filled Polyester

Contact:

BeCu

Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Wire:

28 AWG 7/36 Stranded,
Tinned, Copper with
Gray PVC Insulator

Operating Temp Range:

-40 °C to +105 °C

Current Rating (TCSD/STMM):

2.8 A per pin
(2 pins powered)

Voltage Rating:

300 VAC/424 VDC


Lead Size Accepted:

(0.48 mm) .019" to
(0.53 mm) .021"

Insertion Depth:

(2.87 mm) .113" to
(3.17 mm) .125"

SERIES	NO. PINS PER ROW	END OPTION	OVERALL LENGTH	01	PLATING OPTION	N	OTHER OPTION
TCSD = Socket Strip	-04, -05, -07, -08, -10, -12, -13, -15, -17, -20, -22, -25 (Standard sizes)	-S = Single End -D = Double End	- "XX.XX" = Assembled Length		-F = Gold flash on contact	-N = Notch Polarization	-P "XX" = Position Polarization (Specify "XX" as position number. Same position will be polarized on both ends) -B "XX" = Breakout (Specify "XX" as number of conductors to be broken out) -RW = Reverse Wiring (Blue or black wire opposite position #1) -D "XX" = Daisy Chain -SR = Strain Relief (Not available with -O, -M, -R, -DXX or -BXX) -R = Reversed -M = Middle Reversed (Requires -DXX) -O = Outside Reversed (Requires -DXX)



ALSO AVAILABLE


Contact Samtec

Other sizes

Other platings

POLARIZING KEY


Specify PK-01-07 for polarizing key
(Available in wheels of six each).
Also polarizes SMM Series
socket strips.




Single End (-S)




Double End (-D)



Assembled Length (- "XX.XX")




Position Polarization (-P "XX")




Breakout starts with Number 1
lead indicated by brown wire or
red stripe. Shown on top side.


Breakout (-B "XX")



Reverse Wiring (-RW)




Daisy Chain (-D "XX")



Strain Relief (-SR)



Reversed -R)



Middle Reversed (-M)



Outside Reversed (-O)

Note:

TCSD Series assemblies are
non-standard, non-returnable.