


PVC insulated Flexible cable



Technical & Specification

Cross-section	0.05mm ²
External Dia.	ø0.8mm ±0.05
Construction	10 x ø0.08mm
Material:	
Conductor	Cu blank
Insulator	PVC
Jacket Color	Black/White/Blue/ Red/Yellow+Green/ Grey/Orange/Purple
Dielectric strength	1kv/ 1 minute
Rated voltage	75VDC / 50VAC
Conductor Resistance	399.5Ω/KM at 20°C
Insulator Resistance	15MΩ/KM at 20°C
Flame Class	94V-2
Operating Temperature	-10 ~ 70°C