

6

5

4

3

2

1

MATERIAL AND FINISH:

Insulator: Polycarbonate, UL-94V-0 rated

Contacts: Brass, Nickel plated

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A

Voltage rating: 250 VAC

Insulation resistance: 100 Mohm min. at 500 VDC

Dielectric withstanding voltage: 2000 VAC for one minute

ORDERING CODE:42R32-3

1	2	3	4
---	---	---	---

1) COLOR

1 = BLACK

2 = GRAY

2) TERMINAL OPTIONS

1 = .187(4.8)

2 = .250(6.3)

3) ELECTRICAL CIRCUIT CONFIGURATION

1 = 10A 250V 70°C

2+GROUND








2 = 10A 250V 120°C

2+GROUND



4 = 10A 250V 70°C

2 POLE

**4) PANEL THICKNESS****RECOMMENDED
PANEL CUTOUT**

P/N	A	MAX. PANEL THICKNESS
42R32-3XXX-150	1.5	1.5
42R32-3XXX-200	2.0	2.0
42R32-3XXX-250	2.5	2.5

ADDITIONAL PANEL THICKNESS
AVAILABLE ON REQUESTTOLERANCE
UNLESS OTHERWISE SPECIFIED
X ± 1
X.X ± 0.4
X.XX ± 0.20

DRAWN BY	GQ	DATE:	09/09/01
CHECK BY	TD	DATE:	09/09/01
APPR BY	PB	DATE:	09/09/01

**RoHS
COMPLIANT****Power Dynamics, Inc.**

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: IEC 60320 SINGLE FUSE HOLDER APPL. INLET;
QUICK CONNECT TERMINALS; SNAP-INPART #: **42R32-3XXX-XXX****SHEET
1 of 1**SIZE: A
SCALE: NTS
ALL DIMENSIONS FOR REFERENCE ONLY
DIMENSIONS ARE IN MILLIMETERS

REV:

REVISIONS

CHANGE

DATE

REV

CHNG CHECK APPR

D

C

B

A