

1015-9M-R

NOTE:

MATERIAL: zinc alloy
FINISHED: chromate plated
R=ROHS環保料件

SERIES NO.:

117=D-SUB METAL HOOD

CONTACT NUMBER:

09=09PIN

TYPE OPTION:

V=V TYPE(V型)

CABLE ENTRY SIZE:

DIMENSION OF "X"


A=5.0mm B=6.0mm

C=7.0mm D=8.0mm

E=9.0mm

PARTS OPTION:

SHORT SCREW



UNLESS OTHERWISE SPECIFIED TOLERANCE		Top Willing Co., Ltd.	
ANG.	±0.5		
0.	±0.3		
.00	±0.2		
SCALE:	1:1		
UNIT:	mm		

DRAWN SANDY 04/05/07		DRAWN NAME:	
CHECKED JUDY 04/05/07		鑄鐵殼, V TYPE	
APPROVED TONY 04/05/07		09PIN, V 型, 短螺絲	
DATE / Y2K		PRODUCT NO. R117-09V	
SIZE A4		FILE NAME: R117-09V	
REV. A			
DESCRIPTION			
REV.			