


# Bulkhead Jack

## Right Angle



### Specifications:

|                           |                    |
|---------------------------|--------------------|
| Coaxial Termination       | : Solder           |
| Impedance                 | : 50Ω              |
| Coaxial Cable Types       | : RG-58            |
| Frequency Max             | : 4GHz             |
| Connector Mounting        | : Panel            |
| Body Plating              | : Gold             |
| Centre Contact Resistance | : 4mΩ              |
| Coaxial Connector Type    | : SSMB             |
| Female Contact Material   | : Brass            |
| Female Contact Plating    | : Gold             |
| Insulation Resistance     | : 1,000MΩ          |
| Insulator Material        | : PTFE             |
| Male Contact Material     | : Beryllium Copper |
| Male Contact Plating      | : Gold             |
| No. of Mating Cycles      | : 500              |
| Operating Temperature     | : -65°C to +165°C  |
| Outer Contact Resistance  | : 1mΩ              |
| VSWR                      | : 1.3              |
| Voltage Rating            | : 250V AC          |
| Withstand Voltage         | : 500V             |

