

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0008500004
Status: Active
Description: KK® High Pressure Crimp Terminal 7879, 22-30 AWG, Reel Tin (Sn)

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879 \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	7879
Product Name	KK® High Pressure
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min: Mating (µin)	200
Plating min: Mating (µm)	5.00
Plating min: Termination (µin)	200
Plating min: Termination (µm)	5.00
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm (.062") max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A

Material Info	
Old Part Number	7879-1(P102)

Reference - Drawing Numbers	
Product Specification	PS-7879
Sales Drawing	SD-7879



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
7879Series

Application Tooling FAQ <i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i> Global	
Description	Product #
Hand Crimp Tool	0638190800
Extraction Tool	0011030022
Terminator Die	0011402251
Insertion Tool	0638120000
Mini-Mac™	0638915100
Applicator	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION