




Dimensions: mm (in.)




Top View



Side View

FP: Free Position
OP: Open Position



Circuit Diagram

Electrical Specifications:

- Rating: 1A/30VDC
- Contact resistance: <50mΩ
- Insulation resistance: 100MΩ @ 125VDC
- Dielectric Strength: 125VAC for 1 minute
- Electrical life: 10,000 cycles

Mechanical Specifications:

- Mechanical life: 30,000 cycles
- Operating force: 100gf max.
- Operating temperature: -20°~+70°C

Note:

- RoHS Compliant

Leaf Switch
101-1306-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-1306-EV](#)