





JKL LAMP NUMBER	VOLTS RATED	WATTS	INITIAL MSCP	INITIAL LUMENS	AVERAGE LIFE HRS.	FILAMENT TYPE
6S6-12V	12	6	3.58	45.0	1,500	C-2V
6S6-30V	30	6	3.98	50.0	1,500	C-2V
6S6-120V	120	6	3.18	40.0	1,500	C-7A
6S6-145V	145	6	3.18	40.0	1,500	C-7A
6S6-155V	155	6	3.18	40.0	1,500	C-7A
10S6-230V	230	10	5.97	75.0	1,500	C-1
10S6-250V	250	10	5.97	75.0	1,500	C-1

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
DRAWN BY L. WENGSTROM		APPVD BY DATE Q.C. 3/1/01		TITLE S-6 MINIATURE CANDELABRA SCREW BASE LAMP			
RELEASED		3/1/01		SIZE A	FSCM NO. 55335	DRAWING NO. SCREW BASE CANDELABRA S-6	
REV. NO.		DESCRIPTION/ECO NUMBER		SCALE NONE		RELEASED DATE 3/1/01	
APPVD DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		REVISION DATE		REV. NO.	
						SHEET 1 OF 1	