


view schown without plastic pin and grounding



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 0	D09P80C4G*00	D09P80C6G*00
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 0	D15P80C4G*00	D15P80C6G*00
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 0	D25P80C4G*00	D25P80C6G*00
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 0	D37P80C4G*00	D37P80C6G*00

Gold flash

0,76 » gold

Threaded ØT M3 = L
Threaded ØT 4.40 = X

Threaded ØT M3 = L
Threaded ØT 4.40 = X

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 0	D09P80C4G*00LF	D09P80C6G*00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 0	D15P80C4G*00LF	D15P80C6G*00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 0	D25P80C4G*00LF	D25P80C6G*00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 0	D37P80C4G*00LF	D37P80C6G*00LF

Gold flash

0,76 » gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

rev	ecn no	dr	date
D	-	ATC	1999/07/23
E	LS05-004	MPE	2005/02/14
F	LS06-0095	LGO	2006/06/29
G	LS06-0140	LGO	2006/09/25
H	109-0241	NG	2009-10-27
-	-	-	-

www.fciconnect.com				surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm
				Dr	PESSON	1995-10-27	ANGULAR	0.X	±0.1	size
				Eng	NIRMAL GEORGE	2009-10-27	LINEAR	0.XX	±0.1	A3
				Chr	NIRMAL GEORGE	2009-10-27	0.XX	±0.1	ECN	LS06-0140
				Appr	NIRMAL GEORGE	2009-10-27	Product family	D-SUB	Spec ref	-
				TOLERANCES UNLESS OTHERWISE SPECIFIED						
				European Views						
				Scale						
				2						
				LS06-0140						
				Rev.						
				H						

FCI		MALE CONNECTOR DELTA D USA		C01-8646-0408		Rev.	
right angled press fit		D SUB		H		H	
catalog no		-		CUSTOMER		sheet 1 of 1	