

VG-FPZ Series


for inverter installed home appliances' surge control

[RoHS Compliant]




| Model | Rated voltage AC/DC (V) | Rated current AC/DC (A) | Withstanding voltage 1 min., line to ground AC (V) | Insulation resistance 500VDC 1 min., line to ground (MΩ) min. | Leakage current 250V/60Hz, (mA) max. | Operating temperature range (°C) | Weight (g) |
|---------------|----------------------------|----------------------------|---|---|--|-------------------------------------|---------------|
| VG-2150FPZ-10 | 100 | 15 | 1000 | 300 | 0.5 (125V) | -25~+55 | 200 |
| VG-2150FPZ-20 | 200 | 15 | 1500 | 300 | 1.0 (250V) | -25~+55 | 200 |
| VG-2200FPZ-10 | 100 | 20 | 1000 | 300 | 0.5 (125V) | -25~+55 | 220 |

Shape and Dimensions




*Faston® is a registered trademark of Tyco Electronics AMP. [mm]

Circuit Diagram



Caution: (E) represents a case.

Attenuation Characteristics



- All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact TOKIN for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.