


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2233)
PRT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PRT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

						TITLE		PAN-TY® RELEASABLE LASHING TIES		
						CUSTOMER DRAWING				
						ITEM REVISION NAME		108015LA/01		
						DATASET FILE NAME		108015LA/00 SS-6507.REV09		
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: [IN] mm]				
						.X : .1 (2.5) .XXX : .010 (.25) .XX : .02 (1.5) ANGLES : - - - - -				
9	11/05/13	BWG	RTFI	KJM	CORRECTED TOLERANCES. SEE ECN FOR COMPLETE DETAILS.	SS-6507/09	THIRD ANGLE PROJECTION		MATERIAL:	
8	10/24/13	BWG	RTFI	KJM	UPDATED TITLE BORDER AND NOTE ONE.	SS-6507/08	DRAWING NUMBER:		NYLON 6.6	
REV						DATE	BY	CHK	SCALE	SIZE
DESCRIPTION						ECN	L.VALDES	7-15-77	HVP	NONE
								SHT 1 OF 1		A

2

1

D10100DA/16