


Model 73044
N Type "T" Jack-Plug-Jack Adapter

Model 73044
N Type "T" Jack-Plug-Jack Adapter

Features

- DC – 4GHz bandwidth.
- Connectors are precision machined.
- Meets interface requirements MIL-C-39012.

Materials

Center Conductor:

Male: Brass, Gold Plated

Female: Phosphor Bronze, Gold Plated

Connector Body: Brass, Nickel Plated

Insulators: PTFE

Specifications

Impedance: 50Ω

Frequency Range: DC – 4GHz

Contact Resistance:

Center Conductor: ≤1.0 mΩ

Outer Conductor: ≤0.2 mΩ

Insulation Resistance: ≥ 5000 MΩ

Dielectric Withstand Voltage: 1500V

*For CE compliance, do not hold in hand when
voltages exceed 33 Vrms / 70 Vdc.*

Number of Insertions: 500 cycles minimum

Ordering Information

Model: **73044**

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm),
.xxx = ±.005" (.127 mm). All specifications are to the latest revisions.
Specifications are subject to change without notice. Registered trademarks are
the property of their respective companies.