


UMK- C64M-VS

Order No.: 2970057



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2970057>

VARIOFACE module, for IEC 603/DIN 41612 plug connector, type C, 64-pos., a, c components mounted, with male connector, cable housing with screw interlock

Commercial data

EAN	4017918087579
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.3118 KG
Catalog page information	Page 230 (IF-2002)

Product notes

WEEE/RoHS-compliant since:
09/29/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	125 V
Max. current carrying capacity per branch	1 A
Number of positions	64
Width	135 mm

Height	62.5 mm
Depth	77 mm
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	DIN VDE 0110

Connection data

Connection 1	PCB connection
Connection in acc. with standard	IEC / EN
Type of connection	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3
Connection 2	IEC 603/DIN 41612 connection
Type of connection	Pluggable

Certificates / Approvals



Certification

GOST

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;