

# VS-P1214-P1217-C1000/ 1,0

Order No.: 1608812



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1608812>

Assembled PROFINET-FO cable, round cable, polymer fiber 980/1000 µm, SCRJ/IP67 push-pull plastic housing on SCRJ/IP20, for installation inside buildings, the conductor is suitable for the UV-protected outside insert, length: 1 m

**PROFINET**

| Commercial data          |                    |
|--------------------------|--------------------|
| GTIN (EAN)               | 4046356161343      |
| Note                     | Made-to-order      |
| sales group              | D523               |
| Pack                     | 1 pcs.             |
| Customs tariff           | 85447000           |
| Weight/Piece             | 0.22222 KG         |
| Catalog page information | Page 244 (PC-2009) |

## Product notes

WEEE/RoHS-compliant since:  
01/01/2008



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

| Technical data             |                                |
|----------------------------|--------------------------------|
| Mechanical characteristics |                                |
| Number of positions        | 2                              |
| Connection profile         | SCRJ in acc. with IEC 61754-24 |
| Locking type               | Push Pull                      |

|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Fiber type                      | Polymer Fiber                                   |
| Fiber                           | 980/1000 µm                                     |
| Ferrule diameter                | 2.50 mm                                         |
| Number of fibers                | 2                                               |
| Insertion/withdrawal cycles     | ≥ 500                                           |
| External cable diameter         | 7.5 mm                                          |
| Type of cable                   | Round cable                                     |
| Length of cable                 | 1 m                                             |
| Ambient temperature (operation) | -30 °C ... 70 °C (cable, fixed installation)    |
|                                 | -20 °C ... 60 °C (cable, flexible installation) |
|                                 | (plug/socket)                                   |

#### Material data


|                                     |                       |
|-------------------------------------|-----------------------|
| Housing material                    | PA-GF/PBT             |
| Material, O-ring                    | NBR                   |
| Cable seal material                 | TPE                   |
| Material, housing intermediate seal | NBR                   |
| Outer sheath, material              | LSFH                  |
| External sheath, color              | green-yellow RAL 6018 |
| Ferrule material                    | Copper alloy          |
| Ferrule holder color                | Blue                  |
| Degree of protection                | IP67/IP20             |

#### Optical characteristics

|             |                        |
|-------------|------------------------|
| Attenuation | ≤ 1.7 dB (With 660 nm) |
|-------------|------------------------|

Diagrams/Drawings


Dimensioned drawing



SCRJ connector IP20

SCRJ Push-Pull connector, IP67

Schematic diagram



Pin assignment plug SCRJ

Pin assignment plug SCRJ

**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2010 Phoenix Contact  
Technical modifications reserved;