



770-001A2 and 770-003A2 Type 2 Low Smoke Zero Halogen 90° Right Angle Lipped Adapter Shrink Boots

Type 2 Low Smoke Zero Halogen (LSZH) For Regulated Environmental Safety Applications



Halogen-free polyolefin boots meet low smoke and toxicity requirements of shipboard, transit and aircraft systems. These Low Smoke/Zero Halogen (LSZH) boots fit most standard shrink boot adapters, including M85049 types along with Glenair Series 31 and Series 44 adapters. Oxygen index greater than 30%, smoke index less than 20, and toxicity index under 3 per 100 grams. Material meets requirements of NAVSEA 5617649, VG95343 Part 29, BSG 198-5-DF, EN62329-101 and SAE AS5258 Type G. Good resistance to oils, fuels and solvents. Available with epoxy or hot melt adhesive lining, these 90° boots provide strain relief and environmental protection to connector/cable transitions and aid in efficient routing of wire harnesses and cables. Temperature rating -30° to +135° C. Black color.

- **Low Smoke, Zero Halogen**
- **Meets U.S. and E.U. toxicity requirements.**
- **-30° C to +135° C**

Boot Size	Part Number with Eyelet				Part Number without Eyelet			
	No Adhesive Lining	Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive	Pre-Coated with W2 Standard Hot-Melt Adhesive	Pre-Coated with R Epoxy Adhesive	No Adhesive Lining	Pre-Coated with W1 Hi-Temp Hot-Melt Adhesive	Pre-Coated with W2 Standard Hot-Melt Adhesive	Pre-Coated with R Epoxy Adhesive
02	—	—	—	—	770-003A202	770-003A202W1	770-00A202W2	770-003A202R
03	770-001A203	770-001A203W1	770-001A203W2	770-001A203R	770-003A203	770-003A203W1	770-003A203W2	770-003A203R
04	770-001A204	770-001A204W1	770-001A204W2	770-001A204R	770-003A204	770-003A204W1	770-003A204W2	770-003A204R
05	770-001A205	770-001A205W1	770-001A205W2	770-001A205R	770-003A205	770-003A205W1	770-003A205W2	770-003A205R
06	770-001A206	770-001A206W1	770-001A206W2	770-001A206R	770-003A206	770-003A206W1	770-003A206W2	770-003A206R
07	770-001A207	770-001A207W1	770-001A207W2	770-001A207R	770-003A207	770-003A207W1	770-003A207W2	770-003A207R
08	770-001A208	770-001A208W1	770-001A208W2	770-001A208R	770-003A208	770-003A208W1	770-003A208W2	770-003A208R
09	770-001A209	770-001A209W1	770-001A209W2	770-001A209R	770-003A209	770-003A209W1	770-003A209W2	770-003A209R

Add "-DH" to the end of any part number for drain holes.

Add "-PP" to the end of any part number for potting ports.