




LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			S5	ECR-14-012050	11AUG14	PKS	RRP



- 1 CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 5.59±0.08 [.220±.003] CENTERS.
- 2 SLOT ACCEPTS 0.80–1.20mm [#20–#16.5] AWG COPPER MAGNET WIRE. A SINGLE WIRE ONLY.
- 3 POKE-IN ACCEPTS A 0.50–0.90mm² [#20–#18] AWG SOLID OR FUSED STRANDED LEAD WIRE.
- 4 TIN PLATED
- 5 PAPER SPLICED – RESTRICTED TO BSH GERMANY



OBSOLETE	BRASS	STANDARD	5 62833-6
	PHOSPHOR BRONZE	STANDARD	62833-4
	PHOSPHOR BRONZE	REVERSED	62833-3
	BRASS	REVERSED	62833-2
	BRASS	STANDARD	62833-1
MATERIAL		REELING	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.R. BUCHHEISTER JR. 1/SEP/94		 TE Connectivity							
		CHK MS FEHER 02SEP94									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, POKE-IN, 300 SERIES MAG-MATE —							
		APVD MS FEHER 02SEP94									
		PRODUCT SPEC 108-2012									
		APPLICATION SPEC 114-2046									
		SIZE A2		CAGE CODE 00779		DRAWING NO C=62833		RESTRICTED TO —			
MATERIAL SEE TABLE		FINISH — 		WEIGHT —		SCALE 10:1		SHEET 1 of 1		REV S5	