


- For solid and stranded conductors AWG 27 up to AWG 22
- Max. wire diameter 1.5mm
- Cable diameter 6 to 9mm
- Degree of protection IP65/IP67
- Cat.6 performance class EA suitable for 1/10 Gigabit Ethernet
- Temperature range -40°C up to +70°C
- 750 mating cycles

Data contacts plating: Au 1,27µm (50µ") over Nickel

			Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	Han 3A RJ45 10G connector metal version	Maßstab/ Scale 1:1	
			Detail.	20/10/09				AB
			Insp.					
			Stand.					
36080	20/10/09	AB	HARTING EURL F-95972 Paris			TB 09 45 115 1560	Blatt/ Page 1 / 1	
Mod.	Dot.	Name						Sub.