








Copyright FCI.



PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



TIN LEAD PART NUMBER


SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	--	D09S91C6PI9C
15	39.14	33.32	25.18	24.54	19.18	--	D15S91C6PI9C
25	53.03	47.04	39.12	38.25	33.12	--	D25S91C6PI9C
37	69.32	63.50	55.68	54.71	49.68	--	D37S91C6PI9C
						---	0.76μ gold

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	--	D09S91C6PI9CLF
15	39.14	33.32	25.18	24.54	19.18	--	D15S91C6PI9CLF
25	53.03	47.04	39.12	38.25	33.12	--	D25S91C6PI9CLF
37	69.32	63.50	55.68	54.71	49.68	--	D37S91C6PI9CLF
						---	0.76μ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

rev	ecn no	dr	date
B	-	ATC	1999/03/05
C	LS05-004	MPE	2005/02/11
D	LS06-0089	LGO	2006/06/15
E	LS06-0140	LGO	2006/09/16
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101					
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JOUBERT	1998/04/24	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2:1		
Eng	PESSON	1998/04/24			0.XX	±0.1				
Chr	LEGARE	1998/04/24			0.XXX	±0.1				
Appr	LEGARE	1998/04/24	0.XX* ±2*		0.XXX ±0.1		ECN LS06-0140			
			Product family				D-SUB		Spec ref -	
			title FEMALE CONNECTOR DELTA D STD EUROPE STR PF				dwg no C01-8646-0617		Rev. E	
			catalog no		-		CUSTOMER		sheet 1 of 1	