










NOTES :



Au-VERSION OF CONTACT IS 1-xxxxxx-1
Au-Version des Kontaktes ist 1-xxxxxx-1




WATER TIGHTNESS ACC. GMI 12590: 5.10.3
FURTHER INFORMATIONS SEE PRODUCT SPECIFICATION 108-18102-1/...-9
Wasserdichtheit nach GMI 12590, 5.10.3
Weitere Informationen siehe Produktspezifikation 108-18102-1/...-9



Einfall bis auf 23.5mm zulässig
SHRINKAGE UP TO 23.5MM ALLOWED


JPT		0-0929937-1	1.5 - 2.5	CuFe 2	TINNED	0-0828905-1	WHITE	IPX 9K
JPT		0-0929939-1	0.75 - 1.0	CuFe 2	TINNED	0-0828904-1	LIGHT BLUE	IPX 9K
JPT		0-0929939-1	0.5	CuFe 2	TINNED	0-0963294-1	BLUE	IPX 9K
JPT		0-0929941-1	0.35	CuFe 2	TINNED	0-0963294-1	BLUE	IPX 9K
CONTACT-SYSTEM	ORDER-NO. STRIP	WIRE SIZE [mm 2]	MATERIAL	FINISH	SINGLE WIRE SEAL	COLOR	WATER-TIGHTNESS	




2:1

4114401		5-963217-1 CODING N	E	1	PBT/ASA-GF30	RED	SLIDE	6
4114443	-	4-963217-1 CODING D1	E	1	PBT/ASA-GF30	WHITE	JPT HSG., 16POS.	5
4114435	-	3-963217-1 CODING C1	E	1	PBT/ASA-GF30	RED	SLIDE	6
4114427	-	2-963217-1 CODING B1	F	1	PBT/ASA-GF30	BROWN	JPT HSG., 16POS.	4
4114419	ZFW 16-2	1-963217-1 CODING A1	F	1	PBT/ASA-GF30	RED	SLIDE	6
				1	PBT/ASA-GF30	BLACK	JPT HSG., 16POS.	1
CUSTOMER PART NO.	GM SIGN	PART NO.	REV.	PCS	MATERIAL	COLOR	DESCRIPTION	ITEM NO.


CODING A1




CODING B1





CODING C1



CODING D1



CODING N



2:1

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: S. GARCIA 29-MAR-1999	TE Connectivity
mm	9 PLC ±0.3	CHK: W. STABROTH 29-MAR-1999	NAME: JPT REC-HOUSING, 16POS., ASSY
	3 PLC ±0.3	APVD: -	PRODUCT SPEC: 108-18102
MATERIAL: -	4 PLC ±0.3	FINISH: -	APPLICATION SPEC: 114-18175
	ANGLES: -	WEIGHT: -	SIZE: A1
		CUSTOMER DRAWING	CAGE CODE: 00779
		SCALE: 2:1	DRAWING NO: C=963217
		SHEET: 1 OF 1	RESTRICTED TO: -
		REV: F3	