




| PART NAME | SERIES 60 UPRIGHT ADD-A-RACK | PART No. | 60-2500 TD 60-2513 | REV. DATE | 1-2-02 |
|-----------|------------------------------|----------|--------------------|-----------|--------|
|-----------|------------------------------|----------|--------------------|-----------|--------|

**FINISH**  
 FRAME ASSEMBLY, DOOR, TOP COWLS & TOP COVER \_\_\_\_\_ GRAY TEXTURE OR ROYAL BLUE TEXTURE  
 PANEL MOUNTING RAILS \_\_\_\_\_ SMOOTH BLACK  
**MATERIAL:**  
 PANEL MOUNTING RAILS \_\_\_\_\_ 12 GA. STEEL  
 FRAME TOP, BASE ASSEMBLY, FILLERS & VERTICAL RAILS \_\_\_\_\_ 14 GA. STEEL  
 RAIL SUPPORTS \_\_\_\_\_ 16 GA. STEEL  
 TOP COWLS & TOP COVER \_\_\_\_\_ 18 GA. STEEL  
 DOOR \_\_\_\_\_ 20 GA. STEEL



TOP VIEW

TOP VIEW  
(LESS TOP COVER & TOP COWLS)



FRONT VIEW

SECTION "A-A"


LEFT SIDE VIEW

REAR VIEW

PANEL MOUNTING RAILS (FRONT & REAR) ARE TAPPED #10-32 ON E.I.A. UNIVERSAL SPACING AND ARE FULLY ADJUSTABLE.

BOTTOM PIERCED FOR MOUNTING RC-7758 CASTERS.

LOAD RATING: 1200 LBS. MAX.



BOTTOM VIEW

| PART No. | P.S.   | A      | B      | C      | D      | E      | F      | G      | H      | J      | K      | L      | M      |
|----------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 60-2500  | 21.000 | 29.625 | 22.000 | 20.500 | 17.000 | 29.000 | 26.875 | 18.937 | —      | —      | —      | —      | —      |
| 60-2501  | 31.500 | 40.125 | —      | —      | —      | 39.500 | 37.375 | 29.437 | —      | —      | —      | —      | —      |
| 60-2502  | 42.000 | 50.625 | —      | —      | —      | 50.000 | 47.875 | —      | 19.281 | 17.906 | —      | —      | —      |
| 60-2503  | 52.500 | 61.125 | —      | —      | —      | 60.500 | 58.375 | —      | 24.531 | 23.156 | —      | —      | —      |
| 60-2504  | 61.250 | 69.875 | —      | —      | —      | 69.250 | 67.125 | —      | 28.906 | 27.531 | —      | —      | —      |
| 60-2505  | 70.000 | 78.625 | —      | —      | —      | 78.000 | 75.875 | —      | 33.281 | 31.906 | —      | —      | —      |
| 60-2506  | 78.750 | 87.375 | 22.000 | 20.500 | 17.000 | 86.750 | 84.625 | —      | —      | —      | 25.125 | 22.312 | 23.750 |
| 60-2507  | 21.000 | 29.625 | 25.500 | 24.000 | 20.500 | 29.000 | 26.875 | 18.937 | —      | —      | —      | —      | —      |
| 60-2508  | 31.500 | 40.125 | —      | —      | —      | 39.500 | 37.375 | 29.437 | —      | —      | —      | —      | —      |
| 60-2509  | 42.000 | 50.625 | —      | —      | —      | 50.000 | 47.875 | —      | 19.281 | 17.906 | —      | —      | —      |
| 60-2510  | 52.500 | 61.125 | —      | —      | —      | 60.500 | 58.375 | —      | 24.531 | 23.156 | —      | —      | —      |
| 60-2511  | 61.250 | 69.875 | —      | —      | —      | 69.250 | 67.125 | —      | 28.906 | 27.531 | —      | —      | —      |
| 60-2512  | 70.000 | 78.625 | —      | —      | —      | 78.000 | 75.875 | —      | 33.281 | 31.906 | —      | —      | —      |
| 60-2513  | 78.750 | 87.375 | 25.500 | 24.000 | 20.500 | 86.750 | 84.625 | —      | —      | —      | 25.125 | 22.312 | 23.750 |