


MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH - BASIC


CATALOG LISTING

BZ-2AW8558-D6



CIRCUIT DIAGRAM

BUNA N
ELASTOMER PLUNGER SEAL




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\varnothing .139$ MAX ON $1.000 \pm .002$ CENTERS
- 2 - SUITABLE ONLY FOR APPLICATIONS IMPARTING A RAPID STROKE TO THE SWITCH PLUNGER
- 3 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - 8 1/2 OZ MAX
RELEASE FORCE - - - - 1 1/2 OZ MIN
DIFFERENTIAL TRAVEL - - .008 - .030
OVERTRAVEL - - - - .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SEE CIRCUIT DIAGRAM

L73 15A 125, 250 OR 480 VAC
1A 125 VDC, 0.5A 250 VDC
1/4HP 125 VAC, 1/2HP 250 VAC



SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

CATALOG LISTING
BZ-2AW8558-D6

PAGE 1 OF 1

ISSUE
M
1

REVISIONS

REPLACES X113261-BZ

RELEASE NO. 204448

CHECK

28 NOV 01

SAV

CHECK

28 NOV 01

C SL

RASTER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2AW8558-D6](#)